

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P794031

Luminaire Tested: LER6D55D010-EC6DR6055659030-6LBDP1B

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P794031  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LER6D55D010-EC6DR6055659030-6LBDDP1B  
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 60° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5141.9 lumens  
Efficiency: N/A  
Efficacy: 88.3 lumens/watt  
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 58.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight

TEST NUMBER: P794031

CATALOG NUMBER: LER6D55D010-EC6DR6055659030-6LBDP1B

### Luminous Intensity Polar Plot





TEST NUMBER: P794031

CATALOG NUMBER: LER6D55D010-EC6DR6055659030-6LBDP1B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93			93																
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86			86																
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80			80																
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75			75																
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70			70																
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66			66																
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62			62																
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59			59																
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55			55																
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53			53																

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	667212
5°	683624
10°	691883
15°	659110
20°	581132
25°	470035
30°	317945
35°	159326
40°	25845
45°	25295
50°	25803
55°	26192
60°	26922
65°	27534
70°	28176
75°	28537
80°	27496
85°	22941

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 75°  
 Luminance: 28537 cd/sqm



TEST NUMBER: P794031

CATALOG NUMBER: LER6D55D010-EC6DR6055659030-6LBDP1B

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	595.7	11.6
10°-20°	1611.8	31.3
20°-30°	1734.1	33.7
30°-40°	753.8	14.7
40°-50°	126.6	2.5
50°-60°	123.1	2.4
60°-70°	105.3	2.0
70°-80°	70.5	1.4
80°-90°	21.1	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3941.6	76.7
0°-40°	4695.4	91.3
0°-60°	4945.1	96.2
0°-90°	5141.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5141.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	6107	
5°	6233	596
15°	5827	1612
25°	3899	1734
35°	1194	754
45°	164	127
55°	138	123
65°	106	105
75°	68	70
85°	18	21
90°	0	



TEST NUMBER: P794031

CATALOG NUMBER: LER6D55D010-EC6DR6055659030-6LBDP1B

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	6106.6
2.5°	6278.3
5°	6233.0
7.5°	6247.3
10°	6236.2
12.5°	6107.4
15°	5826.9
17.5°	5450.2
20°	4998.0
22.5°	4514.0
25°	3898.9
27.5°	3118.5
30°	2520.1
32.5°	1942.3
35°	1194.5
37.5°	511.0
40°	181.2
42.5°	166.9
45°	163.7
47.5°	158.1
50°	151.8
52.5°	144.6
55°	137.5
57.5°	130.3
60°	123.2
62.5°	115.2
65°	106.5
67.5°	97.8
70°	88.2
72.5°	77.9
75°	67.6
77.5°	55.6
80°	43.7
82.5°	31.0
85°	18.3
87.5°	6.4
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)