

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P794039

Luminaire Tested: LER6D55D010-EC6DR6055659035-6LBDP1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P794039
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D55D010-EC6DR6055659035-6LBDDP1B
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5196.0 lumens
Efficiency: N/A
Efficacy: 89.3 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 58.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P794039
CATALOG NUMBER: LER6D55D010-EC6DR6055659035-6LBDP1B

Luminous Intensity Polar Plot





TEST NUMBER: P794039

CATALOG NUMBER: LER6D55D010-EC6DR6055659035-6LBDP1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93																			
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86																			
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80																			
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70																			
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66																			
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62																			
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59																			
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55																			
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	674237
5°	690819
10°	699161
15°	666055
20°	587248
25°	474990
30°	321288
35°	160993
40°	26116
45°	25557
50°	26075
55°	26459
60°	27206
65°	27818
70°	28464
75°	28833
80°	27811
85°	23192

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 75°
 Luminance: 28833 cd/sqm



TEST NUMBER: P794039

CATALOG NUMBER: LER6D55D010-EC6DR6055659035-6LBDP1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	602.0	11.6
10°-20°	1628.7	31.3
20°-30°	1752.4	33.7
30°-40°	761.7	14.7
40°-50°	127.9	2.5
50°-60°	124.4	2.4
60°-70°	106.4	2.0
70°-80°	71.2	1.4
80°-90°	21.3	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3983.1	76.7
0°-40°	4744.8	91.3
0°-60°	4997.1	96.2
0°-90°	5196.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5196.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6171	
5°	6299	602
15°	5888	1629
25°	3940	1752
35°	1207	762
45°	165	128
55°	139	124
65°	108	106
75°	68	71
85°	18	21
90°	0	



TEST NUMBER: P794039

CATALOG NUMBER: LER6D55D010-EC6DR6055659035-6LBDP1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	6170.9
2.5°	6344.4
5°	6298.6
7.5°	6313.1
10°	6301.8
12.5°	6171.7
15°	5888.3
17.5°	5507.6
20°	5050.6
22.5°	4561.6
25°	3940.0
27.5°	3151.3
30°	2546.6
32.5°	1962.8
35°	1207.0
37.5°	516.4
40°	183.1
42.5°	168.6
45°	165.4
47.5°	159.8
50°	153.4
52.5°	146.2
55°	138.9
57.5°	131.7
60°	124.5
62.5°	116.4
65°	107.6
67.5°	98.8
70°	89.1
72.5°	78.7
75°	68.3
77.5°	56.2
80°	44.2
82.5°	31.3
85°	18.5
87.5°	6.4
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)