

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P175418

Luminaire Tested: **LDA6A10840D010TE LARL20NF 6LFC1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P175418
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26263)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A10840D010TE LARL20NF 6LFC1
Description: PORTFOLIO 6" Flat Cone, Self-flange Trim Ring, 20° Narrow Flood
Optic, at 0° tilt
Light Source: (1) HIGH LUMEN LED 80CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 960.1 lumens
Efficiency: N/A
Efficacy: 69.4 lumens/watt
Spacing Criteria (0/90/45): 0.35 / 0.35 / 0.34
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 13.84
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P175418

CATALOG NUMBER: LDA6A10840D010TE LARL20NF 6LFC1

Luminous Intensity Polar Plot





TEST NUMBER: P175418

CATALOG NUMBER: LDA6A10840D010TE LARL20NF 6LFC1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	114	112	110	113	111	110	108	107	106	105		104	103	102		100
2	112	109	106	104	110	107	105	103	104	102	101		101	100	98		99
3	109	105	102	99	107	104	101	98	101	99	97		99	97	95		97
4	106	102	98	95	105	101	97	95	99	96	94		97	95	93		95
5	104	99	95	92	102	98	94	92	96	93	91		95	92	90		93
6	101	96	92	90	100	95	92	89	94	91	89		93	90	88		92
7	99	93	90	87	98	93	89	87	92	89	87		91	88	86		90
8	97	91	87	85	96	91	87	85	90	87	85		89	86	84		88
9	95	89	85	83	94	89	85	83	88	85	83		87	84	82		86
10	93	87	84	81	92	87	83	81	86	83	81		85	83	81		85

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	348508
5°	288146
10°	185301
15°	75534
20°	36059
25°	13513
30°	969
35°	187
40°	79
45°	31
50°	34
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P175418

CATALOG NUMBER: LDA6A10840D010TE LARL20NF 6LFC1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	441.6	46.0
10°-20°	404.5	42.1
20°-30°	110.9	11.5
30°-40°	2.7	0.3
40°-50°	0.4	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	956.9	99.7
0°-40°	959.6	100.0
0°-60°	960.1	100.0
0°-90°	960.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	960.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6357	
5°	5236	442
15°	1331	404
25°	223	111
35°	3	3
45°	0	0
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P175418

CATALOG NUMBER: LDA6A10840D010TE LARL20NF 6LFC1

CANDELA DISTRIBUTION (FULL):

0°	
0°	6357.3
1°	6264.6
2°	6059.1
3°	5807.9
4°	5526.1
5°	5236.2
6°	4930.5
7°	4599.9
8°	4222.3
9°	3798.0
10°	3328.8
11°	2832.9
12°	2370.8
13°	1953.7
14°	1615.2
15°	1330.9
17.5°	852.9
20°	618.1
22.5°	417.9
25°	223.4
27.5°	74.8
30°	15.3
32.5°	5.3
35°	2.8
37.5°	1.8
40°	1.1
42.5°	0.7
45°	0.4
47.5°	0.4
50°	0.4
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P175418

CATALOG NUMBER: LDA6A10840D010TE LARL20NF 6LFC1

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°	0.0
87.5°	0.0



(END OF REPORT)