

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P794068

Luminaire Tested: LER6D55D010-EC6DR6555659024-6LBS1H

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P794068
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D55D010-EC6DR6555659024-6LBS1H
Description: 6 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5146.2 lumens
Efficiency: N/A
Efficacy: 88.4 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct


Input Watts (W): 58.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P794068
CATALOG NUMBER: LER6D55D010-EC6DR6555659024-6LBS1H

Luminous Intensity Polar Plot





TEST NUMBER: P794068

CATALOG NUMBER: LER6D55D010-EC6DR6555659024-6LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93			93																
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85			85																
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78			78																
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72			72																
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66			66																
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61			61																
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56			56																
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52			52																
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49			49																
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46			46																

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	272898
5°	272205
10°	271972
15°	263593
20°	239969
25°	209113
30°	173925
35°	137812
40°	99464
45°	62839
50°	32755
55°	17412
60°	9146
65°	5030
70°	2117
75°	2324
80°	1614
85°	1407

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 62839 cd/sqm



TEST NUMBER: P794068

CATALOG NUMBER: LER6D55D010-EC6DR6555659024-6LBS1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	441.9	8.6
10°-20°	1210.0	23.5
20°-30°	1479.1	28.7
30°-40°	1200.1	23.3
40°-50°	598.0	11.6
50°-60°	166.8	3.2
60°-70°	37.9	0.7
70°-80°	9.9	0.2
80°-90°	2.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3131.0	60.8
0°-40°	4331.0	84.2
0°-60°	5095.9	99.0
0°-90°	5146.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5146.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4673	
5°	4643	442
15°	4360	1210
25°	3245	1479
35°	1933	1200
45°	761	598
55°	171	167
65°	36	38
75°	10	10
85°	2	3
90°	0	



TEST NUMBER: P794068

CATALOG NUMBER: LER6D55D010-EC6DR6555659024-6LBS1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	4672.6
2.5°	4669.1
5°	4643.0
7.5°	4627.9
10°	4586.0
12.5°	4500.9
15°	4359.5
17.5°	4138.4
20°	3861.0
22.5°	3561.6
25°	3245.0
27.5°	2906.5
30°	2579.0
32.5°	2255.6
35°	1932.9
37.5°	1610.9
40°	1304.6
42.5°	1017.6
45°	760.8
47.5°	530.1
50°	360.5
52.5°	248.6
55°	171.0
57.5°	115.4
60°	78.3
62.5°	54.2
65°	36.4
67.5°	18.5
70°	12.4
72.5°	11.7
75°	10.3
77.5°	6.9
80°	4.8
82.5°	3.4
85°	2.1
87.5°	1.4
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)