

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P794075

Luminaire Tested: LER6D55D010-EC6DR6555659027-6LBS1B

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P794075
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D55D010-EC6DR6555659027-6LBS1B
Description: 6 INCH ROUND SHALLOW SPECULAR BLACK TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5412.4 lumens
Efficiency: N/A
Efficacy: 93.0 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct


Input Watts (W): 58.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P794075
CATALOG NUMBER: LER6D55D010-EC6DR6555659027-6LBS1B

Luminous Intensity Polar Plot





TEST NUMBER: P794075

CATALOG NUMBER: LER6D55D010-EC6DR6555659027-6LBS1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93			93																
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85			85																
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78			78																
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72			72																
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66			66																
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61			61																
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56			56																
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52			52																
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49			49																
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46			46																

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	287014
5°	286293
10°	286045
15°	277228
20°	252381
25°	219939
30°	182928
35°	144942
40°	104610
45°	66093
50°	34445
55°	18308
60°	9613
65°	5293
70°	2220
75°	2437
80°	1715
85°	1474

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 66093 cd/sqm



TEST NUMBER: P794075

CATALOG NUMBER: LER6D55D010-EC6DR6555659027-6LBS1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	464.7	8.6
10°-20°	1272.6	23.5
20°-30°	1555.6	28.7
30°-40°	1262.2	23.3
40°-50°	629.0	11.6
50°-60°	175.4	3.2
60°-70°	39.9	0.7
70°-80°	10.4	0.2
80°-90°	2.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3293.0	60.8
0°-40°	4555.1	84.2
0°-60°	5359.5	99.0
0°-90°	5412.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5412.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4914	
5°	4883	465
15°	4585	1273
25°	3413	1556
35°	2033	1262
45°	800	629
55°	180	175
65°	38	40
75°	11	10
85°	2	3
90°	0	



TEST NUMBER: P794075

CATALOG NUMBER: LER6D55D010-EC6DR6555659027-6LBS1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	4914.3
2.5°	4910.7
5°	4883.3
7.5°	4867.4
10°	4823.3
12.5°	4733.8
15°	4585.0
17.5°	4352.5
20°	4060.7
22.5°	3745.9
25°	3413.0
27.5°	3056.9
30°	2712.5
32.5°	2372.3
35°	2032.9
37.5°	1694.2
40°	1372.1
42.5°	1070.2
45°	800.2
47.5°	557.5
50°	379.1
52.5°	261.4
55°	179.8
57.5°	121.3
60°	82.3
62.5°	57.1
65°	38.3
67.5°	19.5
70°	13.0
72.5°	12.3
75°	10.8
77.5°	7.2
80°	5.1
82.5°	3.6
85°	2.2
87.5°	1.4
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)