

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P794084

Luminaire Tested: LER6D55D010-EC6DR6555659030-6LBS1H

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P794084
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D55D010-EC6DR6555659030-6LBS1H
Description: 6 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6005.6 lumens
Efficiency: N/A
Efficacy: 103.2 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct

Input Watts (W): 58.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P794084

CATALOG NUMBER: LER6D55D010-EC6DR6555659030-6LBS1H

Luminous Intensity Polar Plot





TEST NUMBER: P794084

CATALOG NUMBER: LER6D55D010-EC6DR6555659030-6LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93			93																
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85			85																
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78			78																
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72			72																
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66			66																
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61			61																
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56			56																
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52			52																
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49			49																
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46			46																

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	318470
5°	317670
10°	317400
15°	307611
20°	280045
25°	244040
30°	202971
35°	160827
40°	116077
45°	73337
50°	38225
55°	20314
60°	10665
65°	5873
70°	2459
75°	2708
80°	1883
85°	1608

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 73337 cd/sqm



TEST NUMBER: P794084

CATALOG NUMBER: LER6D55D010-EC6DR6555659030-6LBS1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	515.7	8.6
10°-20°	1412.1	23.5
20°-30°	1726.1	28.7
30°-40°	1400.5	23.3
40°-50°	697.9	11.6
50°-60°	194.6	3.2
60°-70°	44.2	0.7
70°-80°	11.5	0.2
80°-90°	2.9	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3653.9	60.8
0°-40°	5054.4	84.2
0°-60°	5946.9	99.0
0°-90°	6005.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6005.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5453	
5°	5418	516
15°	5088	1412
25°	3787	1726
35°	2256	1400
45°	888	698
55°	200	195
65°	42	44
75°	12	11
85°	2	3
90°	0	



TEST NUMBER: P794084

CATALOG NUMBER: LER6D55D010-EC6DR6555659030-6LBS1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	5452.9
2.5°	5448.9
5°	5418.5
7.5°	5400.9
10°	5352.0
12.5°	5252.6
15°	5087.5
17.5°	4829.5
20°	4505.8
22.5°	4156.4
25°	3787.0
27.5°	3392.0
30°	3009.7
32.5°	2632.3
35°	2255.7
37.5°	1879.9
40°	1522.5
42.5°	1187.5
45°	887.9
47.5°	618.6
50°	420.7
52.5°	290.1
55°	199.5
57.5°	134.6
60°	91.3
62.5°	63.3
65°	42.5
67.5°	21.6
70°	14.4
72.5°	13.6
75°	12.0
77.5°	8.0
80°	5.6
82.5°	4.0
85°	2.4
87.5°	1.6
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)