

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P794113

Luminaire Tested: LER6D55D010-EC6DR7055659024-6LBDP1LI

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P794113
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D55D010-EC6DR7055659024-6LBDDP1LI
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5913.4 lumens
Efficiency: N/A
Efficacy: 101.6 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 58.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P794113
CATALOG NUMBER: LER6D55D010-EC6DR7055659024-6LBDP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P794113

CATALOG NUMBER: LER6D55D010-EC6DR7055659024-6LBDP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	726409
5°	704824
10°	685171
15°	676179
20°	631420
25°	474351
30°	335330
35°	118777
40°	62458
45°	66520
50°	68893
55°	70177
60°	70626
65°	69132
70°	65233
75°	60452
80°	53671
85°	43501

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 70644 cd/sqm



TEST NUMBER: P794113

CATALOG NUMBER: LER6D55D010-EC6DR7055659024-6LBDP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	606.1	10.3
10°-20°	1662.6	28.1
20°-30°	1831.1	31.0
30°-40°	699.6	11.8
40°-50°	330.3	5.6
50°-60°	328.4	5.6
60°-70°	263.0	4.4
70°-80°	151.1	2.6
80°-90°	41.1	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4099.8	69.3
0°-40°	4799.5	81.2
0°-60°	5458.2	92.3
0°-90°	5913.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5913.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6648	
5°	6426	606
15°	5978	1663
25°	3935	1831
35°	890	700
45°	430	330
55°	368	328
65°	267	263
75°	143	151
85°	35	41
90°	0	



TEST NUMBER: P794113

CATALOG NUMBER: LER6D55D010-EC6DR7055659024-6LBDP1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	6648.4
2.5°	6578.9
5°	6426.3
7.5°	6298.9
10°	6175.7
12.5°	6071.5
15°	5977.8
17.5°	5751.5
20°	5430.5
22.5°	4737.8
25°	3934.7
27.5°	3425.2
30°	2657.9
32.5°	1716.8
35°	890.5
37.5°	481.0
40°	437.9
42.5°	434.7
45°	430.5
47.5°	421.0
50°	405.3
52.5°	387.4
55°	368.4
57.5°	347.4
60°	323.2
62.5°	295.8
65°	267.4
67.5°	235.8
70°	204.2
72.5°	172.6
75°	143.2
77.5°	112.6
80°	85.3
82.5°	60.0
85°	34.7
87.5°	13.7
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)