

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P794114

Luminaire Tested: LER6D55D010-EC6DR7055659024-6LBDP1MW

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P794114
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D55D010-EC6DR7055659024-6LB DP1MW
Description: 6 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4398.9 lumens
Efficiency: N/A
Efficacy: 75.6 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 58.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P794114
CATALOG NUMBER: LER6D55D010-EC6DR7055659024-6LBDP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P794114

CATALOG NUMBER: LER6D55D010-EC6DR7055659024-6LBDP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	540371
5°	524316
10°	509698
15°	503011
20°	469707
25°	352867
30°	249450
35°	88366
40°	46455
45°	49492
50°	51249
55°	52213
60°	52533
65°	51422
70°	48526
75°	44959
80°	39892
85°	32344

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 52546 cd/sqm



TEST NUMBER: P794114

CATALOG NUMBER: LER6D55D010-EC6DR7055659024-6LBDP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	450.9	10.3
10°-20°	1236.8	28.1
20°-30°	1362.2	31.0
30°-40°	520.5	11.8
40°-50°	245.7	5.6
50°-60°	244.3	5.6
60°-70°	195.6	4.4
70°-80°	112.4	2.6
80°-90°	30.5	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3049.9	69.3
0°-40°	3570.3	81.2
0°-60°	4060.4	92.3
0°-90°	4398.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4398.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4946	
5°	4780	451
15°	4447	1237
25°	2927	1362
35°	662	520
45°	320	246
55°	274	244
65°	199	196
75°	106	112
85°	26	31
90°	0	



TEST NUMBER: P794114

CATALOG NUMBER: LER6D55D010-EC6DR7055659024-6LBDP1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	4945.7
2.5°	4894.0
5°	4780.5
7.5°	4685.7
10°	4594.1
12.5°	4516.6
15°	4446.9
17.5°	4278.5
20°	4039.7
22.5°	3524.5
25°	2927.0
27.5°	2548.0
30°	1977.2
32.5°	1277.1
35°	662.5
37.5°	357.9
40°	325.7
42.5°	323.4
45°	320.3
47.5°	313.2
50°	301.5
52.5°	288.2
55°	274.1
57.5°	258.4
60°	240.4
62.5°	220.0
65°	198.9
67.5°	175.4
70°	151.9
72.5°	128.4
75°	106.5
77.5°	83.8
80°	63.4
82.5°	44.6
85°	25.8
87.5°	10.2
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)