

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P794129

Luminaire Tested: LER6D55D010-EC6DR7055659030-6LBDP1LI

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P794129
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D55D010-EC6DR7055659030-6LBDDP1LI
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6901.0 lumens
Efficiency: N/A
Efficacy: 118.6 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 58.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P794129
CATALOG NUMBER: LER6D55D010-EC6DR7055659030-6LBDP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P794129

CATALOG NUMBER: LER6D55D010-EC6DR7055659030-6LBDP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	847721
5°	822531
10°	799612
15°	789113
20°	736868
25°	553569
30°	391334
35°	138611
40°	72884
45°	77630
50°	80383
55°	81892
60°	82404
65°	80662
70°	76127
75°	70541
80°	62606
85°	50772

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 82439 cd/sqm



TEST NUMBER: P794129

CATALOG NUMBER: LER6D55D010-EC6DR7055659030-6LBDP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	707.4	10.3
10°-20°	1940.3	28.1
20°-30°	2136.9	31.0
30°-40°	816.5	11.8
40°-50°	385.5	5.6
50°-60°	383.3	5.6
60°-70°	306.9	4.4
70°-80°	176.4	2.6
80°-90°	47.9	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4784.6	69.3
0°-40°	5601.0	81.2
0°-60°	6369.8	92.3
0°-90°	6901.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6901.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7759	
5°	7500	707
15°	6976	1940
25°	4592	2137
35°	1039	816
45°	502	386
55°	430	383
65°	312	307
75°	167	176
85°	40	48
90°	0	



TEST NUMBER: P794129

CATALOG NUMBER: LER6D55D010-EC6DR7055659030-6LBDP1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	7758.7
2.5°	7677.6
5°	7499.5
7.5°	7350.9
10°	7207.2
12.5°	7085.5
15°	6976.2
17.5°	6712.1
20°	6337.4
22.5°	5529.1
25°	4591.8
27.5°	3997.3
30°	3101.8
32.5°	2003.6
35°	1039.2
37.5°	561.4
40°	511.0
42.5°	507.3
45°	502.4
47.5°	491.4
50°	472.9
52.5°	452.1
55°	429.9
57.5°	405.4
60°	377.1
62.5°	345.2
65°	312.0
67.5°	275.2
70°	238.3
72.5°	201.5
75°	167.1
77.5°	131.4
80°	99.5
82.5°	70.0
85°	40.5
87.5°	16.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)