

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P179548

Luminaire Tested: **LDA6A45827D010TE LARH20SP 6LA1LI**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P179548
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26660)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A45827D010TE LARH20SP 6LA1LI
Description: PORTFOLIO 6" Adjustable Reflector, Angle-cut Trim, Self-flanged, 20° Spot
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3855.8 lumens
Efficiency: N/A
Efficacy: 72.8 lumens/watt
Spacing Criteria (0/90/45): 0.4 / 0.4 / 0.49
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 53
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P179548

CATALOG NUMBER: LDA6A45827D010TE LARH20SP 6LA1LI

Luminous Intensity Polar Plot





TEST NUMBER: P179548

CATALOG NUMBER: LDA6A45827D010TE LARH20SP 6LA1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	115	113	111	109	113	111	109	107	107	105	104	103	102	101	100	99	98	96	96	96	96
2	111	107	104	102	109	106	103	101	103	100	98	100	98	96	97	96	94	93	93	93	93
3	107	103	99	96	106	101	98	95	99	96	94	97	94	92	94	93	91	90	90	90	90
4	104	98	94	91	102	97	94	91	95	92	90	94	91	89	92	90	88	87	87	87	87
5	101	95	90	87	99	94	90	87	92	89	86	91	88	86	89	87	85	84	84	84	84
6	98	91	87	84	96	91	87	84	89	86	83	88	85	83	87	84	82	81	81	81	81
7	95	88	84	81	94	87	83	81	86	83	80	85	82	80	84	82	79	78	78	78	78
8	92	85	81	78	91	85	81	78	84	80	78	83	80	77	82	79	77	76	76	76	76
9	89	82	78	75	88	82	78	75	81	78	75	80	77	75	80	77	75	74	74	74	74
10	87	80	76	73	86	80	76	73	79	75	73	78	75	73	78	75	72	71	71	71	71

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	852476
5°	743439
10°	503804
15°	347760
20°	243359
25°	140397
30°	10375
35°	850
40°	458
45°	279
50°	230
55°	258
60°	296
65°	233
70°	289
75°	191
80°	284
85°	0



TEST NUMBER: P179548

CATALOG NUMBER: LDA6A45827D010TE LARH20SP 6LA1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1147.9	29.8
10°-20°	1726.5	44.8
20°-30°	953.5	24.7
30°-40°	18.8	0.5
40°-50°	3.1	0.1
50°-60°	2.4	0.1
60°-70°	2.1	0.1
70°-80°	1.3	0.0
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3827.9	99.3
0°-40°	3846.7	99.8
0°-60°	3852.2	99.9
0°-90°	3855.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3855.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	15550	
5°	13510	###
15°	6128	1726
25°	2321	954
35°	13	19
45°	4	3
55°	3	2
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P179548

CATALOG NUMBER: LDA6A45827D010TE LARH20SP 6LA1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	15550.4
2.5°	15119.7
5°	13509.8
7.5°	11439.0
10°	9050.5
12.5°	7396.0
15°	6127.5
17.5°	5185.0
20°	4171.5
22.5°	3279.1
25°	2321.1
27.5°	969.8
30°	163.9
32.5°	21.9
35°	12.7
37.5°	8.2
40°	6.4
42.5°	4.6
45°	3.6
47.5°	3.6
50°	2.7
52.5°	2.7
55°	2.7
57.5°	2.7
60°	2.7
62.5°	2.7
65°	1.8
67.5°	1.8
70°	1.8
72.5°	1.8
75°	0.9
77.5°	0.9
80°	0.9
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)