

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P179557

Luminaire Tested: **LDA6A45830D010TE LARH30NF 6LA1LI**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P179557  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26641)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LDA6A45830D010TE LARH30NF 6LA1LI  
Description: PORTFOLIO 6" Adjustable Reflector, Angle-cut Trim, Self-flanged, 30°  
Narrow Flood  
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4675.1 lumens  
Efficiency: N/A  
Efficacy: 88.2 lumens/watt  
Spacing Criteria (0/90/45): 0.56 / 0.56 / 0.55  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct


Input Watts (W): 53  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P179557

CATALOG NUMBER: LDA6A45830D010TE LARH30NF 6LA1LI

### Luminous Intensity Polar Plot





TEST NUMBER: P179557

CATALOG NUMBER: LDA6A45830D010TE LARH30NF 6LA1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	115	113	111	109	112	110	109	107	107	105	104	103	102	101	99	99	98	96			
2	111	107	104	101	109	105	103	100	102	100	98	99	98	96	97	95	94	93			
3	107	102	98	95	105	101	97	95	98	96	93	96	94	92	94	92	90	89			
4	103	98	94	90	102	97	93	90	95	92	89	93	90	88	91	89	87	86			
5	100	94	89	86	99	93	89	86	91	88	85	90	87	85	88	86	84	83			
6	97	90	86	83	96	90	85	82	88	85	82	87	84	81	86	83	81	80			
7	94	87	82	79	93	86	82	79	85	81	79	84	81	78	83	80	78	77			
8	91	84	79	76	90	83	79	76	82	79	76	81	78	76	81	78	75	74			
9	88	81	77	74	87	81	76	74	80	76	73	79	76	73	78	75	73	72			
10	85	78	74	71	85	78	74	71	77	73	71	77	73	71	76	73	71	70			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	767658
5°	707818
10°	630026
15°	477097
20°	284143
25°	156614
30°	37221
35°	2690
40°	773
45°	225
50°	85
55°	96
60°	110
65°	130
70°	160
75°	0
80°	0
85°	0



TEST NUMBER: P179557

CATALOG NUMBER: LDA6A45830D010TE LARH30NF 6LA1LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	1183.2	25.3
10°-20°	2252.0	48.2
20°-30°	1146.2	24.5
30°-40°	88.1	1.9
40°-50°	3.1	0.1
50°-60°	0.9	0.0
60°-70°	1.0	0.0
70°-80°	0.4	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4581.5	98.0
0°-40°	4669.6	99.9
0°-60°	4673.7	100.0
0°-90°	4675.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4675.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	14003	
5°	12862	###
15°	8406	2252
25°	2589	1146
35°	40	88
45°	3	3
55°	1	1
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P179557

CATALOG NUMBER: LDA6A45830D010TE LARH30NF 6LA1LI

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	14003.2
2.5°	13664.1
5°	12862.5
7.5°	12154.0
10°	11318.0
12.5°	10165.5
15°	8406.4
17.5°	6497.4
20°	4870.6
22.5°	3590.7
25°	2589.2
27.5°	1493.5
30°	588.0
32.5°	242.1
35°	40.2
37.5°	20.6
40°	10.8
42.5°	5.9
45°	2.9
47.5°	2.0
50°	1.0
52.5°	1.0
55°	1.0
57.5°	1.0
60°	1.0
62.5°	1.0
65°	1.0
67.5°	1.0
70°	1.0
72.5°	1.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)