

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P794144

Luminaire Tested: LER6D55D010-EC6DR7055659040-6LBDP1H

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P794144
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D55D010-EC6DR7055659040-6LBDP1H
Description: 6 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6952.0 lumens
Efficiency: N/A
Efficacy: 119.5 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 58.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P794144
CATALOG NUMBER: LER6D55D010-EC6DR7055659040-6LBDP1H

Luminous Intensity Polar Plot





TEST NUMBER: P794144

CATALOG NUMBER: LER6D55D010-EC6DR7055659040-6LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	854004
5°	828629
10°	805525
15°	794961
20°	742332
25°	557680
30°	394223
35°	139638
40°	73426
45°	78202
50°	80978
55°	82501
60°	83016
65°	81257
70°	76702
75°	71048
80°	63047
85°	51148

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 83049 cd/sqm



TEST NUMBER: P794144

CATALOG NUMBER: LER6D55D010-EC6DR7055659040-6LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	712.6	10.3
10°-20°	1954.6	28.1
20°-30°	2152.8	31.0
30°-40°	822.5	11.8
40°-50°	388.4	5.6
50°-60°	386.1	5.6
60°-70°	309.1	4.4
70°-80°	177.7	2.6
80°-90°	48.3	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4820.0	69.3
0°-40°	5642.5	81.2
0°-60°	6417.0	92.3
0°-90°	6952.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6952.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7816	
5°	7555	713
15°	7028	1955
25°	4626	2153
35°	1047	822
45°	506	388
55°	433	386
65°	314	309
75°	168	178
85°	41	48
90°	0	



TEST NUMBER: P794144

CATALOG NUMBER: LER6D55D010-EC6DR7055659040-6LBDP1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	7816.2
2.5°	7734.5
5°	7555.1
7.5°	7405.3
10°	7260.5
12.5°	7138.0
15°	7027.9
17.5°	6761.8
20°	6384.4
22.5°	5570.1
25°	4625.9
27.5°	4026.9
30°	3124.7
32.5°	2018.4
35°	1046.9
37.5°	565.5
40°	514.8
42.5°	511.1
45°	506.1
47.5°	495.0
50°	476.4
52.5°	455.4
55°	433.1
57.5°	408.4
60°	379.9
62.5°	347.7
65°	314.3
67.5°	277.2
70°	240.1
72.5°	203.0
75°	168.3
77.5°	132.4
80°	100.2
82.5°	70.5
85°	40.8
87.5°	16.1
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)