

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P794151

Luminaire Tested: LER6D55D010-EC6DR7055659050-6LBDP1B

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P794151  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LER6D55D010-EC6DR7055659050-6LBDDP1B  
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 70° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4073.8 lumens  
Efficiency: N/A  
Efficacy: 70.0 lumens/watt  
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct


Input Watts (W): 58.2  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



Downlight

TEST NUMBER: P794151  
CATALOG NUMBER: LER6D55D010-EC6DR7055659050-6LBDP1B

### Luminous Intensity Polar Plot





TEST NUMBER: P794151  
 CATALOG NUMBER: LER6D55D010-EC6DR7055659050-6LBDP1B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	500425
5°	485556
10°	472021
15°	465830
20°	434988
25°	326779
30°	231005
35°	81830
40°	43031
45°	45830
50°	47458
55°	48346
60°	48643
65°	47622
70°	44948
75°	41624
80°	36934
85°	29962

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 57.5°  
 Luminance: 48662 cd/sqm



TEST NUMBER: P794151

CATALOG NUMBER: LER6D55D010-EC6DR7055659050-6LBDP1B

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	417.6	10.3
10°-20°	1145.4	28.1
20°-30°	1261.5	31.0
30°-40°	482.0	11.8
40°-50°	227.6	5.6
50°-60°	226.3	5.6
60°-70°	181.1	4.4
70°-80°	104.1	2.6
80°-90°	28.3	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2824.4	69.3
0°-40°	3306.4	81.2
0°-60°	3760.2	92.3
0°-90°	4073.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4073.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4580	
5°	4427	418
15°	4118	1145
25°	2711	1261
35°	614	482
45°	297	228
55°	254	226
65°	184	181
75°	99	104
85°	24	28
90°	0	



TEST NUMBER: P794151

CATALOG NUMBER: LER6D55D010-EC6DR7055659050-6LBDP1B

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	4580.1
2.5°	4532.3
5°	4427.1
7.5°	4339.4
10°	4254.5
12.5°	4182.7
15°	4118.2
17.5°	3962.3
20°	3741.1
22.5°	3263.9
25°	2710.6
27.5°	2359.7
30°	1831.0
32.5°	1182.7
35°	613.5
37.5°	331.4
40°	301.7
42.5°	299.5
45°	296.6
47.5°	290.1
50°	279.2
52.5°	266.9
55°	253.8
57.5°	239.3
60°	222.6
62.5°	203.8
65°	184.2
67.5°	162.4
70°	140.7
72.5°	118.9
75°	98.6
77.5°	77.6
80°	58.7
82.5°	41.3
85°	23.9
87.5°	9.4
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)