

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204865

Luminaire Tested: **LSR6B10D010BZ EC6B10209024 6LBCSMB1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P204865  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSR6B10D010BZ EC6B10209024 6LBCSMB1  
Description: PORTFOLIO 6IN CYLINDER  
SHALLOW DISTRIBUTION WITH CAST MATTE BLACK TRIM  
WATTAGE D010TR-10.05 W DE010-10.58 W D5LT-10.2 W DMX-10.6 W DL2-11.8 W  
DL3-11.1 W DLE-11.39 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 712.6 lumens  
Efficiency: N/A  
Efficacy: 72.0 lumens/watt  
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 9.9  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P204865

CATALOG NUMBER: LSR6B10D010BZ EC6B10209024 6LBCSMB1

### Luminous Intensity Polar Plot





TEST NUMBER: P204865

CATALOG NUMBER: LSR6B10D010BZ EC6B10209024 6LBCSMB1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	107	103	100	108	104	101	98	100	98	95	96	94	92	93	91	90	88																			
2	102	95	89	84	99	93	87	83	89	85	81	86	82	79	83	80	77	75																			
3	93	84	77	71	91	83	76	70	80	74	69	77	72	68	74	70	67	65																			
4	86	75	67	61	84	74	66	61	71	65	60	69	63	59	67	62	58	56																			
5	79	67	59	53	77	66	59	53	64	57	52	62	56	52	61	55	51	49																			
6	74	61	53	47	72	60	52	46	58	51	46	57	50	46	55	50	45	43																			
7	68	55	47	41	67	55	47	41	53	46	41	52	45	41	50	45	40	39																			
8	64	51	43	37	62	50	42	37	49	42	37	48	41	37	46	41	36	35																			
9	60	47	39	33	58	46	39	33	45	38	33	44	38	33	43	37	33	31																			
10	56	43	35	30	55	43	35	30	42	35	30	41	34	30	40	34	30	28																			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P204865

CATALOG NUMBER: LSR6B10D010BZ EC6B10209024 6LBCSMB1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	28.5	4.0
10°-20°	81.1	11.4
20°-30°	121.9	17.1
30°-40°	144.6	20.3
40°-50°	143.1	20.1
50°-60°	112.4	15.8
60°-70°	63.0	8.8
70°-80°	17.7	2.5
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	231.4	32.5
0°-40°	376.0	52.8
0°-60°	631.6	88.6
0°-90°	712.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	712.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	301	
5°	300	28
15°	288	81
25°	265	122
35°	232	145
45°	186	143
55°	127	112
65°	63	63
75°	15	18
85°	0	0
90°	0	



TEST NUMBER: P204865

CATALOG NUMBER: LSR6B10D010BZ EC6B10209024 6LBCSMB1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	300.9
2.5°	299.9
5°	300.4
7.5°	297.8
10°	294.8
12.5°	291.2
15°	287.6
17.5°	283.0
20°	276.9
22.5°	270.7
25°	264.6
27.5°	258.0
30°	249.3
32.5°	240.6
35°	231.9
37.5°	221.7
40°	210.0
42.5°	198.7
45°	186.5
47.5°	172.7
50°	158.4
52.5°	142.0
55°	126.7
57.5°	109.3
60°	93.0
62.5°	78.2
65°	62.8
67.5°	49.6
70°	36.8
72.5°	25.0
75°	15.3
77.5°	7.7
80°	2.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)