

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P794232

Luminaire Tested: LER6D60D010-EC6DR3055659035-6LBDP1H

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P794232
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D60D010-EC6DR3055659035-6LBDP1H
Description: 6 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 30° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7065.5 lumens
Efficiency: N/A
Efficacy: 109.7 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.49
Luminous Opening: Rectangular (W 0.38' x L: 0.38' x H: 0')
CIE Type: Direct

Input Watts (W): 64.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P794232

CATALOG NUMBER: LER6D60D010-EC6DR3055659035-6LBDP1H

Luminous Intensity Polar Plot





TEST NUMBER: P794232

CATALOG NUMBER: LER6D60D010-EC6DR3055659035-6LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96																			
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92																			
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89																			
4	103	98	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	85																			
5	100	94	89	86	98	93	89	86	91	88	85	90	86	84	88	86	83	82																			
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79																			
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77																			
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74																			
9	88	81	76	73	87	80	76	73	80	76	73	79	75	73	78	75	73	72																			
10	85	78	74	71	85	78	74	71	77	73	71	76	73	71	76	73	70	69																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1738989	1738989	1738989
5°	1689066	1687099	1689150
10°	1462987	1452673	1462645
15°	954528	949401	944631
20°	474643	492449	474007
25°	239096	269610	234189
30°	95729	104303	83409
35°	44404	42526	35648
40°	19175	21283	18056
45°	13520	16779	13639
50°	4644	12218	4918
55°	2682	5058	2829
60°	1883	2220	1883
65°	1213	1213	1213
70°	739	492	739
75°	0	325	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°

Vertical Angle: 45°

Luminance: 16779 cd/sqm



TEST NUMBER: P794232

CATALOG NUMBER: LER6D60D010-EC6DR3055659035-6LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1997.8	28.3
10°-20°	3217.5	45.5
20°-30°	1390.4	19.7
30°-40°	316.9	4.5
40°-50°	108.8	1.5
50°-60°	26.6	0.4
60°-70°	6.9	0.1
70°-80°	0.7	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6605.6	93.5
0°-40°	6922.5	98.0
0°-60°	7057.9	99.9
0°-90°	7065.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7065.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	22719	22719	22719	22719	22719	
5°	21983	21962	21957	22003	21984	1999
15°	12046	11900	11981	11942	11921	3225
25°	2831	2938	3192	2863	2773	1355
35°	475	485	455	452	382	322
45°	125	155	155	155	126	89
55°	20	21	38	22	21	20
65°	7	7	7	7	7	7
75°	0	0	1	0	0	1
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P794232

CATALOG NUMBER: LER6D60D010-EC6DR3055659035-6LBDP1H

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	22719.0	22719.0	22719.0	22719.0	22719.0
2.5°	22568.4	22552.8	22561.7	22572.9	22577.3
5°	21982.8	21961.6	21957.2	22002.9	21983.9
7.5°	20801.6	20771.5	20725.7	20829.5	20926.5
10°	18822.8	18789.4	18690.1	18739.2	18818.4
12.5°	15901.5	15793.3	15791.1	15947.2	15926.1
15°	12045.5	11900.5	11980.8	11941.8	11920.6
17.5°	8100.2	8044.5	8151.5	8119.2	7979.8
20°	5827.0	5841.5	6045.6	5943.0	5819.2
22.5°	4252.0	4304.4	4546.5	4282.1	4185.1
25°	2831.0	2938.0	3192.3	2863.3	2772.9
27.5°	1741.2	1790.3	2047.9	1718.9	1669.8
30°	1083.1	1058.5	1180.1	1012.8	943.7
32.5°	710.5	679.3	718.3	644.7	588.9
35°	475.2	485.2	455.1	451.7	381.5
37.5°	296.7	341.3	301.2	321.2	245.4
40°	191.9	247.6	213.0	235.4	180.7
42.5°	157.3	190.7	175.1	186.3	160.6
45°	124.9	155.0	155.0	155.0	126.0
47.5°	69.2	103.7	132.7	106.0	73.6
50°	39.0	52.4	102.6	54.7	41.3
52.5°	26.8	30.1	70.3	31.2	27.9
55°	20.1	21.2	37.9	22.3	21.2
57.5°	15.6	16.7	20.1	16.7	15.6
60°	12.3	12.3	14.5	13.4	12.3
62.5°	8.9	8.9	10.0	8.9	8.9
65°	6.7	6.7	6.7	6.7	6.7
67.5°	3.3	4.5	4.5	4.5	4.5
70°	3.3	2.2	2.2	2.2	3.3
72.5°	2.2	1.1	1.1	1.1	1.1
75°	0.0	0.0	1.1	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - 90°-270°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)