

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203318

Luminaire Tested: **LSR6B10D010BZ EC6B10209024 6LBMWH1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P203318  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSR6B10D010BZ EC6B10209024 6LBMWH1  
Description: PORTFOLIO 6IN CYLINDER  
MEDIUM DISTRIBUTION WITH WHEAT TRIM  
WATTAGE D010TR-10.05 W DE010-10.58 W D5LT-10.2 W DMX-10.6 W DL2-11.8 W  
DL3-11.1 W DLE-11.39 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 606.1 lumens  
Efficiency: N/A  
Efficacy: 61.2 lumens/watt  
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.85  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 9.9  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P203318

CATALOG NUMBER: LSR6B10D010BZ EC6B10209024 6LBMWH1

### Luminous Intensity Polar Plot





TEST NUMBER: P203318

CATALOG NUMBER: LSR6B10D010BZ EC6B10209024 6LBMWH1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	114	111	108	106	111	109	106	104	105	103	101	101	100	98	97	96	95	94					94			
2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	93	91	89	87					87			
3	103	96	91	87	101	95	90	87	92	88	85	90	87	84	88	85	83	81					81			
4	97	90	85	80	96	89	84	80	87	82	79	85	81	78	83	80	77	76					76			
5	93	84	79	74	91	83	78	74	82	77	73	80	76	73	78	75	72	71					71			
6	88	79	73	69	87	78	73	69	77	72	68	76	71	68	74	70	67	66					66			
7	84	75	69	64	82	74	68	64	73	68	64	71	67	64	70	66	63	62					62			
8	80	70	64	60	78	70	64	60	69	64	60	68	63	60	67	62	59	58					58			
9	76	66	61	57	75	66	60	57	65	60	56	64	59	56	63	59	56	55					55			
10	72	63	57	53	71	62	57	53	62	57	53	61	56	53	60	56	53	52					52			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P203318

CATALOG NUMBER: LSR6B10D010BZ EC6B10209024 6LBMWH1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	69.1	11.4
10°-20°	169.7	28.0
20°-30°	196.3	32.4
30°-40°	125.5	20.7
40°-50°	35.6	5.9
50°-60°	6.4	1.0
60°-70°	2.6	0.4
70°-80°	0.9	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	435.2	71.8
0°-40°	560.7	92.5
0°-60°	602.6	99.4
0°-90°	606.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	606.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	756	
5°	743	69
15°	609	170
25°	433	196
35°	198	126
45°	41	36
55°	6	6
65°	2	3
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P203318

CATALOG NUMBER: LSR6B10D010BZ EC6B10209024 6LBMWH1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	756.1
2.5°	755.3
5°	742.6
7.5°	719.9
10°	687.8
12.5°	650.7
15°	608.6
17.5°	564.8
20°	521.8
22.5°	479.6
25°	433.3
27.5°	382.7
30°	326.2
32.5°	263.0
35°	198.1
37.5°	143.3
40°	99.5
42.5°	65.7
45°	41.3
47.5°	24.4
50°	14.3
52.5°	8.4
55°	5.9
57.5°	5.1
60°	4.2
62.5°	3.4
65°	2.5
67.5°	1.7
70°	1.7
72.5°	0.8
75°	0.8
77.5°	0.8
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)