

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P202597

Luminaire Tested: **LSR6B10D010BZ EC6B10209024 6LBMWMH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P202597
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR6B10D010BZ EC6B10209024 6LBMWMH1
Description: PORTFOLIO 6IN CYLINDER
MEDIUM DISTRIBUTION WITH WARM HAZE TRIM
WATTAGE D010TR-10.05 W DE010-10.58 W D5LT-10.2 W DMX-10.6 W DL2-11.8 W
DL3-11.1 W DLE-11.39 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 602.3 lumens
Efficiency: N/A
Efficacy: 60.8 lumens/watt
Spacing Criteria (0/90/45): 0.9 / 0.9 / 0.89
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P202597

CATALOG NUMBER: LSR6B10D010BZ EC6B10209024 6LBMWMH1

Luminous Intensity Polar Plot





TEST NUMBER: P202597

CATALOG NUMBER: LSR6B10D010BZ EC6B10209024 6LBMWMH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93																			
2	108	103	99	95	105	101	97	94	98	95	92	95	92	90	92	90	88	86																			
3	102	95	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80																			
4	97	89	83	79	95	88	83	79	86	81	78	84	80	77	82	79	76	74																			
5	92	83	77	73	90	82	77	73	80	76	72	79	75	71	77	74	71	69																			
6	87	78	72	67	85	77	71	67	76	71	67	74	70	66	73	69	66	64																			
7	83	73	67	63	81	72	67	63	71	66	62	70	65	62	69	65	62	60																			
8	78	69	63	58	77	68	62	58	67	62	58	66	61	58	65	61	58	56																			
9	75	65	59	55	73	64	59	55	63	58	54	62	58	54	62	57	54	53																			
10	71	61	55	51	70	61	55	51	60	55	51	59	54	51	58	54	51	50																			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P202597

CATALOG NUMBER: LSR6B10D010BZ EC6B10209024 6LBMWMH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	61.5	10.2
10°-20°	157.8	26.2
20°-30°	193.8	32.2
30°-40°	132.9	22.1
40°-50°	42.7	7.1
50°-60°	8.7	1.4
60°-70°	3.4	0.6
70°-80°	1.3	0.2
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	413.2	68.6
0°-40°	546.1	90.7
0°-60°	597.5	99.2
0°-90°	602.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	602.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	670	
5°	657	61
15°	565	158
25°	428	194
35°	212	133
45°	51	43
55°	9	9
65°	4	3
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P202597

CATALOG NUMBER: LSR6B10D010BZ EC6B10209024 6LBMWMH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	669.9
2.5°	665.8
5°	657.1
7.5°	640.7
10°	618.8
12.5°	591.7
15°	564.6
17.5°	534.5
20°	501.2
22.5°	466.5
25°	427.7
27.5°	384.7
30°	330.6
32.5°	270.8
35°	212.0
37.5°	158.4
40°	113.9
42.5°	77.7
45°	50.6
47.5°	31.2
50°	18.9
52.5°	11.8
55°	8.7
57.5°	6.6
60°	5.1
62.5°	4.1
65°	3.6
67.5°	2.6
70°	2.0
72.5°	1.5
75°	1.0
77.5°	1.0
80°	0.5
82.5°	0.5
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)