

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P794266

Luminaire Tested: LER6D60D010-EC6DR3555659027-6LBDP1MW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P794266
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-20)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D60D010-EC6DR3555659027-6LB DP1MW
Description: 6 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 35° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6224.9 lumens
Efficiency: N/A
Efficacy: 96.7 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.54
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 64.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P794266
CATALOG NUMBER: LER6D60D010-EC6DR3555659027-6LBDP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P794266

CATALOG NUMBER: LER6D60D010-EC6DR3555659027-6LBDP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20																		
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																			
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																												
1	115	112	110	108	112	110	108	107	106	105	103	103	101	100	99	98	98	96																												
2	110	106	103	101	108	105	102	99	102	99	97	99	97	95	96	95	93	92																												
3	106	101	97	94	105	100	96	93	97	95	92	95	93	91	93	91	89	88																												
4	103	97	92	89	101	96	92	89	94	90	88	92	89	87	90	88	86	84																												
5	99	93	88	85	98	92	87	84	90	86	84	89	85	83	87	84	82	81																												
6	96	89	84	81	94	88	84	81	87	83	80	85	82	80	84	81	79	78																												
7	93	85	81	78	91	85	80	77	84	80	77	83	79	77	82	79	76	75																												
8	90	82	78	74	88	82	77	74	81	77	74	80	76	74	79	76	73	72																												
9	87	79	75	72	86	79	75	72	78	74	71	77	74	71	77	73	71	70																												
10	84	77	72	69	83	76	72	69	76	72	69	75	71	69	74	71	69	68																												

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1871385
5°	1827413
10°	1646986
15°	1278325
20°	725043
25°	282077
30°	105233
35°	57688
40°	37697
45°	22946
50°	14601
55°	10325
60°	7561
65°	4111
70°	288
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 22946 cd/sqm



TEST NUMBER: P794266

CATALOG NUMBER: LER6D60D010-EC6DR3555659027-6LBDP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1532.4	24.6
10°-20°	2991.9	48.1
20°-30°	1220.2	19.6
30°-40°	292.0	4.7
40°-50°	121.7	2.0
50°-60°	50.4	0.8
60°-70°	15.8	0.3
70°-80°	0.4	0.0
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5744.4	92.3
0°-40°	6036.4	97.0
0°-60°	6208.5	99.7
0°-90°	6224.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6224.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	17128	
5°	16662	###
15°	11301	2992
25°	2340	1220
35°	432	292
45°	148	122
55°	54	50
65°	16	16
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P794266

CATALOG NUMBER: LER6D60D010-EC6DR3555659027-6LBDP1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	17127.7
2.5°	17025.0
5°	16661.6
7.5°	15936.8
10°	14844.9
12.5°	13307.4
15°	11301.1
17.5°	8847.3
20°	6235.7
22.5°	3976.3
25°	2339.8
27.5°	1322.6
30°	834.1
32.5°	585.7
35°	432.5
37.5°	334.4
40°	264.3
42.5°	203.6
45°	148.5
47.5°	111.2
50°	85.9
52.5°	68.2
55°	54.2
57.5°	43.9
60°	34.6
62.5°	25.2
65°	15.9
67.5°	5.6
70°	0.9
72.5°	0.9
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.9
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)