

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203730

Luminaire Tested: **LSR6B10D010BZ EC6B10209024 6LBNWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203730
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR6B10D010BZ EC6B10209024 6LBNWH1
Description: PORTFOLIO 6IN CYLINDER
NARROW DISTRIBUTION WITH WHEAT TRIM
WATTAGE D010TR-10.05 W DE010-10.58 W D5LT-10.2 W DMX-10.6 W DL2-11.8 W
DL3-11.1 W DLE-11.39 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 517.3 lumens
Efficiency: N/A
Efficacy: 52.3 lumens/watt
Spacing Criteria (0/90/45): 0.56 / 0.56 / 0.64
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203730

CATALOG NUMBER: LSR6B10D010BZ EC6B10209024 6LBNWH1

Luminous Intensity Polar Plot





TEST NUMBER: P203730

CATALOG NUMBER: LSR6B10D010BZ EC6B10209024 6LBNWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	111	109	107	112	109	107	105	105	104	102	101	100	99	98	97	96	94		
2	109	104	101	97	107	103	99	96	99	97	94	96	94	92	94	92	90	89		
3	104	98	93	90	102	97	92	89	94	91	88	92	89	86	89	87	85	83		
4	99	92	87	83	97	91	86	83	89	85	82	87	84	81	85	82	80	79		
5	95	87	82	78	93	86	81	77	84	80	77	83	79	76	81	78	75	74		
6	91	82	77	73	89	82	76	73	80	76	72	79	75	72	78	74	71	70		
7	87	78	73	69	85	77	72	69	76	72	68	75	71	68	74	70	67	66		
8	83	74	69	65	82	74	68	65	73	68	65	72	67	64	71	67	64	63		
9	79	71	65	62	78	70	65	61	69	65	61	68	64	61	68	64	61	60		
10	76	67	62	58	75	67	62	58	66	61	58	65	61	58	65	61	58	57		

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203730

CATALOG NUMBER: LSR6B10D010BZ EC6B10209024 6LBNWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	86.0	16.6
10°-20°	165.2	31.9
20°-30°	150.2	29.0
30°-40°	91.0	17.6
40°-50°	20.7	4.0
50°-60°	2.6	0.5
60°-70°	1.2	0.2
70°-80°	0.4	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	401.3	77.6
0°-40°	492.4	95.2
0°-60°	515.7	99.7
0°-90°	517.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	517.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1016	
5°	957	86
15°	595	165
25°	326	150
35°	144	91
45°	23	21
55°	3	3
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P203730

CATALOG NUMBER: LSR6B10D010BZ EC6B10209024 6LBNWH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1015.5
2.5°	1003.2
5°	957.4
7.5°	883.5
10°	789.4
12.5°	691.7
15°	594.9
17.5°	506.9
20°	433.0
22.5°	373.1
25°	325.6
27.5°	283.4
30°	242.0
32.5°	193.6
35°	144.3
37.5°	101.2
40°	66.9
42.5°	41.4
45°	22.9
47.5°	10.6
50°	4.4
52.5°	3.5
55°	2.6
57.5°	2.6
60°	1.8
62.5°	1.8
65°	0.9
67.5°	0.9
70°	0.9
72.5°	0.9
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)