

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204142

Luminaire Tested: **LSR6B10D010BZ EC6B10209024 6LBSH1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P204142  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSR6B10D010BZ EC6B10209024 6LBSH1  
Description: PORTFOLIO 6IN CYLINDER  
SHALLOW DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM  
WATTAGE D010TR-10.05 W DE010-10.58 W D5LT-10.2 W DMX-10.6 W DL2-11.8 W  
DL3-11.1 W DLE-11.39 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 799.7 lumens  
Efficiency: N/A  
Efficacy: 80.8 lumens/watt  
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 9.9  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P204142

CATALOG NUMBER: LSR6B10D010BZ EC6B10209024 6LBSH1

### Luminous Intensity Polar Plot





TEST NUMBER: P204142

CATALOG NUMBER: LSR6B10D010BZ EC6B10209024 6LBSH1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	102	96	90	85	100	94	88	84	90	86	82	87	83	80	84	81	79	77			
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67			
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58			
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51			
6	75	63	55	49	73	62	54	49	60	54	49	59	53	48	57	52	48	46			
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41			
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37			
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34			
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P204142

CATALOG NUMBER: LSR6B10D010BZ EC6B10209024 6LBSH1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	39.2	4.9
10°-20°	106.5	13.3
20°-30°	147.9	18.5
30°-40°	161.4	20.2
40°-50°	150.5	18.8
50°-60°	114.3	14.3
60°-70°	62.6	7.8
70°-80°	17.2	2.2
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	293.5	36.7
0°-40°	454.9	56.9
0°-60°	719.6	90.0
0°-90°	799.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	799.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	418	
5°	415	39
15°	380	106
25°	321	148
35°	258	161
45°	196	151
55°	128	114
65°	62	63
75°	15	17
85°	0	0
90°	0	



TEST NUMBER: P204142

CATALOG NUMBER: LSR6B10D010BZ EC6B10209024 6LBSH1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	418.2
2.5°	418.2
5°	414.7
7.5°	409.4
10°	401.5
12.5°	390.9
15°	379.5
17.5°	365.4
20°	352.2
22.5°	336.3
25°	321.4
27.5°	306.4
30°	289.7
32.5°	273.8
35°	258.0
37.5°	242.1
40°	227.1
42.5°	211.3
45°	195.5
47.5°	179.6
50°	162.0
52.5°	145.3
55°	127.7
57.5°	110.9
60°	94.2
62.5°	77.5
65°	62.5
67.5°	48.4
70°	36.1
72.5°	24.7
75°	15.0
77.5°	7.0
80°	1.8
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)