

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204554

Luminaire Tested: **LSR6B10D010BZ EC6B10209024 6LBSMW1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P204554  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSR6B10D010BZ EC6B10209024 6LBSMW1  
Description: PORTFOLIO 6IN CYLINDER  
SHALLOW DISTRIBUTION WITH MATTE WHITE TRIM  
WATTAGE D010TR-10.05 W DE010-10.58 W D5LT-10.2 W DMX-10.6 W DL2-11.8 W  
DL3-11.1 W DLE-11.39 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 833.9 lumens  
Efficiency: N/A  
Efficacy: 84.2 lumens/watt  
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.34  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 9.9  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P204554

CATALOG NUMBER: LSR6B10D010BZ EC6B10209024 6LBSMW1

### Luminous Intensity Polar Plot





TEST NUMBER: P204554

CATALOG NUMBER: LSR6B10D010BZ EC6B10209024 6LBSMW1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	110	106	102	99	107	104	100	97	99	97	94	96	93	91	92	90	88	86																			
2	101	93	87	82	98	92	86	81	88	83	79	85	81	77	82	79	76	74																			
3	93	83	75	69	90	81	74	69	78	72	67	76	70	66	73	69	65	63																			
4	85	74	65	59	83	72	65	59	70	63	58	68	62	57	66	61	56	54																			
5	78	66	58	51	76	65	57	51	63	56	51	61	55	50	59	54	49	47																			
6	73	60	51	45	71	59	51	45	57	50	44	55	49	44	54	48	44	42																			
7	67	54	46	40	66	54	46	40	52	45	40	51	44	39	49	43	39	37																			
8	63	50	41	36	61	49	41	36	48	41	35	46	40	35	45	39	35	33																			
9	59	46	38	32	57	45	37	32	44	37	32	43	36	32	42	36	32	30																			
10	55	42	34	29	54	42	34	29	41	34	29	40	33	29	39	33	29	27																			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P204554

CATALOG NUMBER: LSR6B10D010BZ EC6B10209024 6LBSMW1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	31.8	3.8
10°-20°	90.7	10.9
20°-30°	136.7	16.4
30°-40°	162.6	19.5
40°-50°	162.3	19.5
50°-60°	132.0	15.8
60°-70°	81.2	9.7
70°-80°	31.5	3.8
80°-90°	5.1	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	259.3	31.1
0°-40°	421.9	50.6
0°-60°	716.2	85.9
0°-90°	833.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	833.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	336	
5°	335	32
15°	322	91
25°	297	137
35°	260	163
45°	211	162
55°	148	132
65°	82	81
75°	29	31
85°	4	5
90°	0	



TEST NUMBER: P204554

CATALOG NUMBER: LSR6B10D010BZ EC6B10209024 6LBSMW1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	336.0
2.5°	336.5
5°	335.0
7.5°	333.0
10°	330.6
12.5°	326.1
15°	322.2
17.5°	316.2
20°	309.8
22.5°	303.9
25°	297.4
27.5°	288.6
30°	279.7
32.5°	271.3
35°	260.4
37.5°	248.5
40°	237.7
42.5°	224.3
45°	211.0
47.5°	196.7
50°	181.3
52.5°	165.5
55°	147.7
57.5°	130.4
60°	113.6
62.5°	97.3
65°	81.5
67.5°	66.7
70°	52.9
72.5°	40.0
75°	28.7
77.5°	18.8
80°	11.4
82.5°	6.9
85°	4.0
87.5°	2.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)