

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204969

Luminaire Tested: **LSR6B10D010BZ EC6B10209027 6LBSCMMS1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P204969  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSR6B10D010BZ EC6B10209027 6LBCSMMS1  
Description: PORTFOLIO 6IN CYLINDER  
SHALLOW DISTRIBUTION WITH CAST MATTE METALLIC SILVER TRIM  
WATTAGE D010TR-10.05 W DE010-10.58 W D5LT-10.2 W DMX-10.6 W DL2-11.8 W  
DL3-11.1 W DLE-11.39 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 897.7 lumens  
Efficiency: N/A  
Efficacy: 90.7 lumens/watt  
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.27  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 9.9  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P204969

CATALOG NUMBER: LSR6B10D010BZ EC6B10209027 6LBCSMMS1

### Luminous Intensity Polar Plot





TEST NUMBER: P204969

CATALOG NUMBER: LSR6B10D010BZ EC6B10209027 6LBCSMMS1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	107	103	100	108	105	101	98	100	98	95	97	94	92	93	91	90	88																			
2	102	95	89	84	99	93	88	83	90	85	81	86	83	79	83	80	78	76																			
3	94	85	77	72	92	83	76	71	80	74	70	77	73	69	75	71	67	65																			
4	87	76	68	62	84	74	67	61	72	66	61	70	64	60	68	63	59	57																			
5	80	68	60	54	78	67	59	54	65	58	53	63	57	53	61	56	52	50																			
6	74	62	54	48	72	61	53	47	59	52	47	58	51	47	56	51	46	44																			
7	69	56	48	42	67	56	48	42	54	47	42	53	46	42	51	46	41	40																			
8	64	52	44	38	63	51	43	38	50	43	38	48	42	38	47	42	37	36																			
9	60	48	40	35	59	47	40	34	46	39	34	45	39	34	44	38	34	32																			
10	57	44	36	31	55	43	36	31	43	36	31	42	35	31	41	35	31	29																			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P204969

CATALOG NUMBER: LSR6B10D010BZ EC6B10209027 6LBCSMMS1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	38.9	4.3
10°-20°	109.0	12.1
20°-30°	159.2	17.7
30°-40°	182.1	20.3
40°-50°	175.0	19.5
50°-60°	135.1	15.1
60°-70°	75.4	8.4
70°-80°	22.0	2.4
80°-90°	1.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	307.1	34.2
0°-40°	489.2	54.5
0°-60°	799.4	89.0
0°-90°	897.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	897.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	412	
5°	409	39
15°	387	109
25°	346	159
35°	292	182
45°	228	175
55°	152	135
65°	76	75
75°	19	22
85°	1	1
90°	0	



TEST NUMBER: P204969

CATALOG NUMBER: LSR6B10D010BZ EC6B10209027 6LBCSMMS1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	412.2
2.5°	412.2
5°	408.8
7.5°	407.0
10°	401.2
12.5°	394.2
15°	386.7
17.5°	379.2
20°	368.1
22.5°	359.4
25°	346.1
27.5°	332.7
30°	319.3
32.5°	306.0
35°	291.5
37.5°	277.0
40°	260.1
42.5°	245.0
45°	228.2
47.5°	209.0
50°	191.0
52.5°	171.3
55°	151.5
57.5°	131.2
60°	112.1
62.5°	92.9
65°	75.5
67.5°	59.2
70°	44.1
72.5°	30.8
75°	19.2
77.5°	9.9
80°	3.5
82.5°	1.2
85°	0.6
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)