

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P35126

Luminaire Tested: **LSR6B10D010BZ EC6B10209027 6LBMWH1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P35126  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSR6B10D010BZ EC6B10209027 6LBMWH1  
Description: PORTFOLIO 6IN CYLINDER  
MEDIUM DISTRIBUTION WITH WHEAT TRIM  
WATTAGE D010TR-10.05 W DE010-10.58 W D5LT-10.2 W DMX-10.6 W DL2-11.8 W  
DL3-11.1 W DLE-11.39 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 719.0 lumens  
Efficiency: N/A  
Efficacy: 74.1 lumens/watt  
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.85  
Luminous Opening: Circular (Dia: 0.46' x H: 0')  
CIE Type: Direct


Input Watts (W): 9.7  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P35126

CATALOG NUMBER: LSR6B10D010BZ EC6B10209027 6LBMWH1

### Luminous Intensity Polar Plot





TEST NUMBER: P35126

CATALOG NUMBER: LSR6B10D010BZ EC6B10209027 6LBMWH1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	108	106	111	109	106	104	105	103	101	101	100	98	97	96	95	94			
2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	92	91	89	87			
3	103	96	91	87	101	95	90	87	92	88	85	90	87	84	88	85	83	81			
4	97	90	85	80	96	89	84	80	87	82	79	85	81	78	83	80	77	76			
5	93	84	79	74	91	83	78	74	82	77	73	80	76	73	78	75	72	71			
6	88	79	73	69	87	78	73	69	77	72	68	76	71	68	74	70	67	66			
7	84	75	69	64	82	74	68	64	73	68	64	71	67	64	70	66	63	62			
8	80	70	64	60	78	70	64	60	69	64	60	68	63	60	67	62	59	58			
9	76	66	61	57	75	66	60	57	65	60	56	64	59	56	63	59	56	55			
10	72	63	57	53	71	62	57	53	62	57	53	61	56	53	60	56	53	52			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	58521
5°	57697
10°	54058
15°	48765
20°	42976
25°	37000
30°	29154
35°	18716
40°	10050
45°	4521
50°	1725
55°	796
60°	652
65°	463
70°	382
75°	252
80°	0
85°	0



TEST NUMBER: P35126

CATALOG NUMBER: LSR6B10D010BZ EC6B10209027 6LBMWH1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	82.0	11.4
10°-20°	201.3	28.0
20°-30°	232.9	32.4
30°-40°	148.9	20.7
40°-50°	42.2	5.9
50°-60°	7.5	1.0
60°-70°	3.1	0.4
70°-80°	1.1	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	516.3	71.8
0°-40°	665.1	92.5
0°-60°	714.9	99.4
0°-90°	719.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	719.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	897	
5°	881	82
15°	722	201
25°	514	233
35°	235	149
45°	49	42
55°	7	8
65°	3	3
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P35126

CATALOG NUMBER: LSR6B10D010BZ EC6B10209027 6LBMWH1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	897
2.5°	896
5°	881
7.5°	854
10°	816
12.5°	772
15°	722
17.5°	670
20°	619
22.5°	569
25°	514
27.5°	454
30°	387
32.5°	312
35°	235
37.5°	170
40°	118
42.5°	78
45°	49
47.5°	29
50°	17
52.5°	10
55°	7
57.5°	6
60°	5
62.5°	4
65°	3
67.5°	2
70°	2
72.5°	1
75°	1
77.5°	1
80°	0
82.5°	0
85°	0
87.5°	0
90°	0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)