

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P794383

Luminaire Tested: LER6D60D010-EC6DR4555659040-6LBDP1B

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P794383
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-36)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D60D010-EC6DR4555659040-6LBDP1B
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 45° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6837.8 lumens
Efficiency: N/A
Efficacy: 106.2 lumens/watt
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.69
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 64.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P794383

CATALOG NUMBER: LER6D60D010-EC6DR4555659040-6LBDP1B

Luminous Intensity Polar Plot





TEST NUMBER: P794383
 CATALOG NUMBER: LER6D60D010-EC6DR4555659040-6LBDP1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100	
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	98	98	97	95			95	
2	109	105	102	99	107	103	100	98	100	98	95	97	95	93	95	93	91	90			90	
3	105	99	95	91	103	98	94	91	95	92	89	93	90	88	91	89	87	85			85	
4	100	94	89	85	99	93	88	85	91	87	84	89	86	83	87	84	82	81			81	
5	96	89	84	80	95	88	83	80	86	82	79	85	81	79	83	80	78	77			77	
6	92	85	80	76	91	84	79	76	83	78	75	81	77	75	80	77	74	73			73	
7	89	81	75	72	87	80	75	72	79	74	71	78	74	71	77	73	71	69			69	
8	85	77	72	68	84	76	71	68	75	71	68	74	70	67	73	70	67	66			66	
9	82	73	68	65	81	73	68	65	72	68	65	71	67	64	71	67	64	63			63	
10	79	70	65	62	78	70	65	62	69	65	62	68	64	61	68	64	61	60			60	

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1320515
5°	1282916
10°	1227399
15°	1123334
20°	891185
25°	556378
30°	306666
35°	137691
40°	54228
45°	25557
50°	12120
55°	6343
60°	3125
65°	750
70°	319
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 25557 cd/sqm



TEST NUMBER: P794383

CATALOG NUMBER: LER6D60D010-EC6DR4555659040-6LBDP1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1099.1	16.1
10°-20°	2704.9	39.6
20°-30°	2142.0	31.3
30°-40°	713.3	10.4
40°-50°	141.6	2.1
50°-60°	32.2	0.5
60°-70°	4.7	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5946.0	87.0
0°-40°	6659.3	97.4
0°-60°	6833.0	99.9
0°-90°	6837.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6837.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	12086	
5°	11697	###
15°	9931	2705
25°	4615	2142
35°	1032	713
45°	165	142
55°	33	32
65°	3	5
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P794383

CATALOG NUMBER: LER6D60D010-EC6DR4555659040-6LBDP1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	12085.9
2.5°	12007.0
5°	11697.1
7.5°	11441.4
10°	11063.0
12.5°	10559.2
15°	9930.9
17.5°	8986.0
20°	7664.6
22.5°	6090.5
25°	4615.1
27.5°	3379.4
30°	2430.7
32.5°	1653.1
35°	1032.3
37.5°	612.2
40°	380.2
42.5°	250.0
45°	165.4
47.5°	106.5
50°	71.3
52.5°	47.5
55°	33.3
57.5°	21.9
60°	14.3
62.5°	7.6
65°	2.9
67.5°	1.0
70°	1.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)