

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P794403

Luminaire Tested: LER6D60D010-EC6DR5055659024-6LBS1B

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P794403  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-44)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LER6D60D010-EC6DR5055659024-6LBS1B  
Description: 6 INCH ROUND SHALLOW SPECULAR BLACK TRIM, WITH 50° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6339.2 lumens  
Efficiency: N/A  
Efficacy: 98.4 lumens/watt  
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.73  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct


Input Watts (W): 64.4  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



Downlight

TEST NUMBER: P794403  
CATALOG NUMBER: LER6D60D010-EC6DR5055659024-6LBS1B

### Luminous Intensity Polar Plot





TEST NUMBER: P794403

CATALOG NUMBER: LER6D60D010-EC6DR5055659024-6LBS1B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100														
1	114	112	109	107	112	110	108	106	106	104	102	102	101	99	98	97	97	95					95														
2	109	105	101	98	107	103	100	97	100	98	95	97	95	93	95	93	91	90					90														
3	105	99	95	91	103	98	94	90	95	92	89	93	90	88	91	88	86	85					85														
4	100	94	89	85	99	93	88	85	90	87	84	89	85	83	87	84	82	80					80														
5	96	89	84	80	95	88	83	79	86	82	79	85	81	78	83	80	77	76					76														
6	92	84	79	75	91	83	79	75	82	78	74	81	77	74	79	76	74	72					72														
7	88	80	75	71	87	79	74	71	78	74	71	77	73	70	76	73	70	69					69														
8	85	76	71	67	84	76	71	67	75	70	67	74	70	67	73	69	66	65					65														
9	81	73	68	64	80	72	67	64	71	67	64	71	67	64	70	66	63	62					62														
10	78	70	64	61	77	69	64	61	68	64	61	68	64	61	67	63	60	59					59														

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1115989
5°	1104294
10°	1086109
15°	988988
20°	822944
25°	584178
30°	309201
35°	126007
40°	46797
45°	21416
50°	8788
55°	4591
60°	2251
65°	672
70°	0
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 21416 cd/sqm



TEST NUMBER: P794403

CATALOG NUMBER: LER6D60D010-EC6DR5055659024-6LBS1B

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	951.7	15.0
10°-20°	2405.1	37.9
20°-30°	2160.4	34.1
30°-40°	676.4	10.7
40°-50°	118.4	1.9
50°-60°	23.6	0.4
60°-70°	3.6	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5517.2	87.0
0°-40°	6193.6	97.7
0°-60°	6335.6	99.9
0°-90°	6339.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6339.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	10214	
5°	10068	952
15°	8743	2405
25°	4846	2160
35°	945	676
45°	139	118
55°	24	24
65°	3	4
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P794403

CATALOG NUMBER: LER6D60D010-EC6DR5055659024-6LBS1B

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	10214.0
2.5°	10163.2
5°	10068.5
7.5°	9923.8
10°	9789.5
12.5°	9358.9
15°	8743.2
17.5°	7961.3
20°	7077.7
22.5°	6055.6
25°	4845.7
27.5°	3562.6
30°	2450.8
32.5°	1595.7
35°	944.7
37.5°	542.5
40°	328.1
42.5°	213.6
45°	138.6
47.5°	84.4
50°	51.7
52.5°	35.3
55°	24.1
57.5°	16.4
60°	10.3
62.5°	6.0
65°	2.6
67.5°	0.9
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)