

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P35123

Luminaire Tested: **LSR6B10D010BZ EC6B10209027 6LBWB1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P35123
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR6B10D010BZ EC6B10209027 6LBWB1
Description: PORTFOLIO 6IN CYLINDER
WIDE DISTRIBUTION WITH SPECULAR BLACK TRIM
WATTAGE D010TR-10.05 W DE010-10.58 W D5LT-10.2 W DMX-10.6 W DL2-11.8 W
DL3-11.1 W DLE-11.39 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 490.9 lumens
Efficiency: N/A
Efficacy: 50.6 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.08 / 1.08
Luminous Opening: Circular (Dia: 0.46' x H: 0')
CIE Type: Direct


Input Watts (W): 9.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P35123

CATALOG NUMBER: LSR6B10D010BZ EC6B10209027 6LBWB1

Luminous Intensity Polar Plot





TEST NUMBER: P35123

CATALOG NUMBER: LSR6B10D010BZ EC6B10209027 6LBWB1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20																	
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																								
RCR																																																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																																				
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92																																				
2	106	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84																																				
3	100	93	87	83	98	92	86	82	89	85	81	86	83	80	84	81	78	77																																				
4	94	86	79	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																																				
5	89	79	73	68	87	78	72	67	76	71	67	75	70	66	73	69	66	64																																				
6	83	73	67	62	82	72	66	61	71	65	61	69	64	61	68	64	60	59																																				
7	78	68	61	56	77	67	61	56	66	60	56	65	60	56	63	59	55	54																																				
8	74	63	57	52	73	63	56	52	61	56	52	60	55	51	59	55	51	50																																				
9	70	59	52	48	69	58	52	48	57	52	48	57	51	47	56	51	47	46																																				
10	66	55	49	44	65	55	49	44	54	48	44	53	48	44	52	47	44	42																																				

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	24139
5°	24035
10°	23849
15°	23302
20°	22703
25°	21452
30°	19587
35°	16885
40°	12945
45°	8765
50°	4973
55°	2047
60°	261
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P35123

CATALOG NUMBER: LSR6B10D010BZ EC6B10209027 6LBWB1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	34.8	7.1
10°-20°	97.3	19.8
20°-30°	136.3	27.8
30°-40°	130.1	26.5
40°-50°	74.1	15.1
50°-60°	18.1	3.7
60°-70°	0.2	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	268.3	54.7
0°-40°	398.5	81.2
0°-60°	490.7	100.0
0°-90°	490.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	490.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	370	
5°	367	35
15°	345	97
25°	298	136
35°	212	130
45°	95	74
55°	18	18
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P35123

CATALOG NUMBER: LSR6B10D010BZ EC6B10209027 6LBWB1

CANDELA DISTRIBUTION (FULL):

	0°
0°	370
2.5°	370
5°	367
7.5°	363
10°	360
12.5°	354
15°	345
17.5°	337
20°	327
22.5°	314
25°	298
27.5°	280
30°	260
32.5°	236
35°	212
37.5°	183
40°	152
42.5°	123
45°	95
47.5°	70
50°	49
52.5°	31
55°	18
57.5°	8
60°	2
62.5°	0
65°	0
67.5°	0
70°	0
72.5°	0
75°	0
77.5°	0
80°	0
82.5°	0
85°	0
87.5°	0
90°	0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)