

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P794495

Luminaire Tested: LER6D60D010-EC6DR6055659024-6LBDP1B

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P794495  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LER6D60D010-EC6DR6055659024-6LBDDP1B  
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 60° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4845.0 lumens  
Efficiency: N/A  
Efficacy: 75.2 lumens/watt  
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct


Input Watts (W): 64.4  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



Downlight

TEST NUMBER: P794495  
CATALOG NUMBER: LER6D60D010-EC6DR6055659024-6LBDP1B

### Luminous Intensity Polar Plot





TEST NUMBER: P794495

CATALOG NUMBER: LER6D60D010-EC6DR6055659024-6LBDP1B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93			93																
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86			86																
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80			80																
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75			75																
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70			70																
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66			66																
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62			62																
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59			59																
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55			55																
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53			53																

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	628697
5°	644161
10°	651931
15°	621058
20°	547587
25°	442898
30°	299588
35°	150122
40°	24347
45°	23842
50°	24307
55°	24668
60°	25370
65°	25931
70°	26547
75°	26891
80°	25923
85°	21562

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 75°  
 Luminance: 26891 cd/sqm



TEST NUMBER: P794495

CATALOG NUMBER: LER6D60D010-EC6DR6055659024-6LBDP1B

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	561.3	11.6
10°-20°	1518.7	31.3
20°-30°	1634.0	33.7
30°-40°	710.3	14.7
40°-50°	119.3	2.5
50°-60°	116.0	2.4
60°-70°	99.2	2.0
70°-80°	66.4	1.4
80°-90°	19.9	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3714.0	76.7
0°-40°	4424.3	91.3
0°-60°	4659.6	96.2
0°-90°	4845.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4845.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	5754	
5°	5873	561
15°	5490	1519
25°	3674	1634
35°	1126	710
45°	154	119
55°	130	116
65°	100	99
75°	64	66
85°	17	20
90°	0	



TEST NUMBER: P794495

CATALOG NUMBER: LER6D60D010-EC6DR6055659024-6LBDP1B

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	5754.1
2.5°	5915.8
5°	5873.2
7.5°	5886.6
10°	5876.1
12.5°	5754.8
15°	5490.5
17.5°	5135.5
20°	4709.5
22.5°	4253.4
25°	3673.8
27.5°	2938.4
30°	2374.6
32.5°	1830.2
35°	1125.5
37.5°	481.5
40°	170.7
42.5°	157.3
45°	154.3
47.5°	149.0
50°	143.0
52.5°	136.3
55°	129.5
57.5°	122.8
60°	116.1
62.5°	108.6
65°	100.3
67.5°	92.1
70°	83.1
72.5°	73.4
75°	63.7
77.5°	52.4
80°	41.2
82.5°	29.2
85°	17.2
87.5°	6.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)