

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203735

Luminaire Tested: **LSR6B10D010BZ EC6B10209727 6LBNWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203735
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR6B10D010BZ EC6B10209727 6LBNWH1
Description: PORTFOLIO 6IN CYLINDER
NARROW DISTRIBUTION WITH WHEAT TRIM
WATTAGE D010TR-10.05 W DE010-10.58 W D5LT-10.2 W DMX-10.6 W DL2-11.8 W
DL3-11.1 W DLE-11.39 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 511.3 lumens
Efficiency: N/A
Efficacy: 51.6 lumens/watt
Spacing Criteria (0/90/45): 0.56 / 0.56 / 0.64
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203735

CATALOG NUMBER: LSR6B10D010BZ EC6B10209727 6LBNWH1

Luminous Intensity Polar Plot





TEST NUMBER: P203735

CATALOG NUMBER: LSR6B10D010BZ EC6B10209727 6LBNWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR	0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100	100	100		
	1	114	111	109	107	112	109	107	105	105	104	102	101	100	99	98	97	96	94	94	94	94	94	94		
	2	109	104	101	97	107	103	99	96	99	97	94	96	94	92	94	92	90	89	89	87	85	85	89		
	3	104	98	93	90	102	97	92	89	94	91	88	92	89	86	89	87	85	83	83	81	85	83	83		
	4	99	92	87	83	97	91	86	83	89	85	82	87	84	81	85	82	80	79	79	78	80	79	79		
	5	95	87	82	78	93	86	81	77	84	80	77	83	79	76	81	78	75	74	74	78	75	74	74		
	6	91	82	77	73	89	82	76	73	80	76	72	79	75	72	78	74	71	70	70	74	71	70	70		
	7	87	78	73	69	85	77	72	69	76	72	68	75	71	68	74	70	67	66	66	74	70	67	66		
	8	83	74	69	65	82	74	68	65	73	68	65	72	67	64	71	67	64	63	63	71	67	64	63		
	9	79	71	65	62	78	70	65	61	69	65	61	68	64	61	68	64	61	60	60	68	64	61	60		
	10	76	67	62	58	75	67	62	58	66	61	58	65	61	58	65	61	58	57	57	65	61	58	57		

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203735

CATALOG NUMBER: LSR6B10D010BZ EC6B10209727 6LBNWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	85.0	16.6
10°-20°	163.3	31.9
20°-30°	148.5	29.0
30°-40°	90.0	17.6
40°-50°	20.5	4.0
50°-60°	2.6	0.5
60°-70°	1.2	0.2
70°-80°	0.4	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	396.7	77.6
0°-40°	486.7	95.2
0°-60°	509.8	99.7
0°-90°	511.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	511.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1004	
5°	946	85
15°	588	163
25°	322	148
35°	143	90
45°	23	20
55°	3	3
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P203735

CATALOG NUMBER: LSR6B10D010BZ EC6B10209727 6LBNWH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1003.9
2.5°	991.8
5°	946.5
7.5°	873.4
10°	780.4
12.5°	683.8
15°	588.1
17.5°	501.1
20°	428.0
22.5°	368.9
25°	321.9
27.5°	280.1
30°	239.2
32.5°	191.4
35°	142.7
37.5°	100.0
40°	66.1
42.5°	40.9
45°	22.6
47.5°	10.4
50°	4.3
52.5°	3.5
55°	2.6
57.5°	2.6
60°	1.7
62.5°	1.7
65°	0.9
67.5°	0.9
70°	0.9
72.5°	0.9
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)