

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204654

Luminaire Tested: **LSR6B10D010BZ EC6B10208030 6LBPSMW1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P204654  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSR6B10D010BZ EC6B10208030 6LBPSMW1  
Description: PORTFOLIO 6IN CYLINDER  
SHALLOW DISTRIBUTION WITH PLASTIC MATTE WHITE TRIM  
WATTAGE D010TR-10.05 W DE010-10.58 W D5LT-10.2 W DMX-10.6 W DL2-11.8 W  
DL3-11.1 W DLE-11.39 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1154.5 lumens  
Efficiency: N/A  
Efficacy: 116.6 lumens/watt  
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.34  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 9.9  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P204654

CATALOG NUMBER: LSR6B10D010BZ EC6B10208030 6LBPSMW1

### Luminous Intensity Polar Plot





TEST NUMBER: P204654

CATALOG NUMBER: LSR6B10D010BZ EC6B10208030 6LBPSMW1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	110	106	102	99	107	104	100	97	99	97	94	96	93	91	92	90	88	86																			
2	101	93	87	82	98	92	86	81	88	83	79	85	81	77	82	79	76	74																			
3	93	83	75	69	90	81	74	69	78	72	67	76	70	66	73	69	65	63																			
4	85	74	66	59	83	72	65	59	70	63	58	68	62	57	66	61	56	54																			
5	78	66	58	51	76	65	57	51	63	56	51	61	55	50	59	54	49	47																			
6	73	60	51	45	71	59	51	45	57	50	44	55	49	44	54	48	44	42																			
7	67	54	46	40	66	54	46	40	52	45	40	51	44	39	49	43	39	37																			
8	63	50	41	36	61	49	41	36	48	41	35	46	40	35	45	39	35	33																			
9	59	46	38	32	57	45	37	32	44	37	32	43	36	32	42	36	32	30																			
10	55	42	34	29	54	42	34	29	41	34	29	40	33	29	39	33	29	27																			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P204654

CATALOG NUMBER: LSR6B10D010BZ EC6B10208030 6LBPSMW1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	44.1	3.8
10°-20°	125.6	10.9
20°-30°	189.2	16.4
30°-40°	225.1	19.5
40°-50°	224.7	19.5
50°-60°	182.8	15.8
60°-70°	112.4	9.7
70°-80°	43.6	3.8
80°-90°	7.0	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	358.9	31.1
0°-40°	584.1	50.6
0°-60°	991.5	85.9
0°-90°	1154.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1154.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	465	
5°	464	44
15°	446	126
25°	412	189
35°	360	225
45°	292	225
55°	204	183
65°	113	112
75°	40	44
85°	6	7
90°	0	



TEST NUMBER: P204654

CATALOG NUMBER: LSR6B10D010BZ EC6B10208030 6LBPSMW1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	465.2
2.5°	465.8
5°	463.8
7.5°	461.1
10°	457.6
12.5°	451.5
15°	446.0
17.5°	437.8
20°	428.9
22.5°	420.7
25°	411.8
27.5°	399.5
30°	387.2
32.5°	375.5
35°	360.5
37.5°	344.1
40°	329.0
42.5°	310.6
45°	292.1
47.5°	272.3
50°	251.0
52.5°	229.2
55°	204.5
57.5°	180.6
60°	157.3
62.5°	134.8
65°	112.9
67.5°	92.3
70°	73.2
72.5°	55.4
75°	39.7
77.5°	26.0
80°	15.7
82.5°	9.6
85°	5.5
87.5°	2.7
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)