

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P205369

Luminaire Tested: **LSR6B10D010BZ EC6B10208030 6LBSLI1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P205369
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR6B10D010BZ EC6B10208030 6LBSL11
Description: PORTFOLIO 6IN CYLINDER
SHALLOW DISTRIBUTION WITH SPECULAR CLEAR TRIM
WATTAGE D010TR-10.05 W DE010-10.58 W D5LT-10.2 W DMX-10.6 W DL2-11.8 W
DL3-11.1 W DLE-11.39 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1146.0 lumens
Efficiency: N/A
Efficacy: 115.8 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 1.04
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P205369

CATALOG NUMBER: LSR6B10D010BZ EC6B10208030 6LBSLI1

Luminous Intensity Polar Plot





TEST NUMBER: P205369

CATALOG NUMBER: LSR6B10D010BZ EC6B10208030 6LBSLI1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	111	107	104	101	109	105	102	99	101	99	96	97	95	93	94	92	91	89					89			
2	103	96	91	86	100	94	89	85	91	87	83	88	84	81	85	82	79	77					77			
3	95	86	79	74	93	85	78	73	82	76	72	79	75	71	77	73	70	68					68			
4	88	78	70	64	86	77	69	64	74	68	63	72	67	62	70	65	62	60					60			
5	82	71	63	57	80	70	62	57	67	61	56	66	60	55	64	59	55	53					53			
6	76	64	56	51	74	63	56	51	62	55	50	60	54	50	59	53	49	47					47			
7	71	59	51	46	70	58	51	45	57	50	45	55	49	45	54	49	45	43					43			
8	67	54	47	41	65	54	46	41	52	46	41	51	45	41	50	45	41	39					39			
9	63	50	43	38	61	50	43	38	49	42	38	48	42	37	47	41	37	36					36			
10	59	47	40	35	58	46	39	35	45	39	35	45	39	34	44	38	34	33					33			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P205369

CATALOG NUMBER: LSR6B10D010BZ EC6B10208030 6LBSLI1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	66.6	5.8
10°-20°	169.6	14.8
20°-30°	216.3	18.9
30°-40°	224.4	19.6
40°-50°	206.7	18.0
50°-60°	155.5	13.6
60°-70°	83.9	7.3
70°-80°	22.5	2.0
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	452.6	39.5
0°-40°	677.0	59.1
0°-60°	1039.2	90.7
0°-90°	1146.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1146.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	723	
5°	712	67
15°	605	170
25°	470	216
35°	358	224
45°	269	207
55°	174	156
65°	84	84
75°	20	23
85°	0	0
90°	0	



TEST NUMBER: P205369

CATALOG NUMBER: LSR6B10D010BZ EC6B10208030 6LBSLI1

CANDELA DISTRIBUTION (FULL):

	0°
0°	723.2
2.5°	720.8
5°	712.2
7.5°	696.4
10°	668.4
12.5°	640.4
15°	605.1
17.5°	572.2
20°	538.1
22.5°	502.8
25°	470.0
27.5°	438.3
30°	409.1
32.5°	382.3
35°	357.9
37.5°	334.8
40°	312.9
42.5°	289.8
45°	269.1
47.5°	245.9
50°	222.8
52.5°	198.5
55°	174.1
57.5°	149.8
60°	126.6
62.5°	104.7
65°	84.0
67.5°	64.5
70°	47.5
72.5°	32.9
75°	19.5
77.5°	8.5
80°	2.4
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)