

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P794514

Luminaire Tested: LER6D60D010-EC6DR6055659030-6LBDP1MW

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P794514
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D60D010-EC6DR6055659030-6LBDP1MW
Description: 6 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6502.5 lumens
Efficiency: N/A
Efficacy: 101.0 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 64.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P794514

CATALOG NUMBER: LER6D60D010-EC6DR6055659030-6LBDP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P794514

CATALOG NUMBER: LER6D60D010-EC6DR6055659030-6LBDP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93	93	93	93
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86	86	86	86
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80	80	80	80
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75	75	75	75
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70	70	70	70
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66	66	66	66
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62	62	62	62
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59	59	59	59
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55	55	55	55
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53	53	53	53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	843766
5°	864516
10°	874956
15°	833511
20°	734903
25°	594413
30°	402070
35°	201475
40°	32676
45°	31985
50°	32636
55°	33126
60°	34046
65°	34824
70°	35651
75°	36052
80°	34795
85°	28959

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 75°
 Luminance: 36052 cd/sqm



TEST NUMBER: P794514

CATALOG NUMBER: LER6D60D010-EC6DR6055659030-6LBDP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	753.3	11.6
10°-20°	2038.2	31.3
20°-30°	2193.0	33.7
30°-40°	953.2	14.7
40°-50°	160.1	2.5
50°-60°	155.7	2.4
60°-70°	133.2	2.0
70°-80°	89.1	1.4
80°-90°	26.6	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4984.5	76.7
0°-40°	5937.8	91.3
0°-60°	6253.5	96.2
0°-90°	6502.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6502.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7722	
5°	7882	753
15°	7369	2038
25°	4931	2193
35°	1510	953
45°	207	160
55°	174	156
65°	135	133
75°	85	89
85°	23	27
90°	0	



TEST NUMBER: P794514

CATALOG NUMBER: LER6D60D010-EC6DR6055659030-6LBDP1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	7722.5
2.5°	7939.6
5°	7882.3
7.5°	7900.4
10°	7886.3
12.5°	7723.5
15°	7368.7
17.5°	6892.3
20°	6320.5
22.5°	5708.4
25°	4930.6
27.5°	3943.6
30°	3186.9
32.5°	2456.2
35°	1510.5
37.5°	646.2
40°	229.1
42.5°	211.1
45°	207.0
47.5°	200.0
50°	192.0
52.5°	182.9
55°	173.9
57.5°	164.8
60°	155.8
62.5°	145.7
65°	134.7
67.5°	123.6
70°	111.6
72.5°	98.5
75°	85.4
77.5°	70.4
80°	55.3
82.5°	39.2
85°	23.1
87.5°	8.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)