

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P794530

Luminaire Tested: LER6D60D010-EC6DR6055659040-6LBDP1MW

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P794530  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LER6D60D010-EC6DR6055659040-6LBDP1MW  
Description: 6 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 60° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6878.2 lumens  
Efficiency: N/A  
Efficacy: 106.8 lumens/watt  
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct


Input Watts (W): 64.4  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



Downlight

TEST NUMBER: P794530  
CATALOG NUMBER: LER6D60D010-EC6DR6055659040-6LBDP1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P794530

CATALOG NUMBER: LER6D60D010-EC6DR6055659040-6LBDP1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93																			
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86																			
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80																			
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70																			
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66																			
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62																			
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59																			
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55																			
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	892518
5°	914463
10°	925503
15°	881675
20°	777366
25°	628747
30°	425297
35°	213119
40°	34573
45°	33839
50°	34506
55°	35031
60°	36012
65°	36841
70°	37696
75°	38162
80°	36809
85°	30714

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 75°  
 Luminance: 38162 cd/sqm



TEST NUMBER: P794530

CATALOG NUMBER: LER6D60D010-EC6DR6055659040-6LBDP1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	796.9	11.6
10°-20°	2156.0	31.3
20°-30°	2319.7	33.7
30°-40°	1008.3	14.7
40°-50°	169.4	2.5
50°-60°	164.7	2.4
60°-70°	140.9	2.0
70°-80°	94.3	1.4
80°-90°	28.2	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5272.5	76.7
0°-40°	6280.9	91.3
0°-60°	6614.9	96.2
0°-90°	6878.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6878.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	8169	
5°	8338	797
15°	7794	2156
25°	5215	2320
35°	1598	1008
45°	219	169
55°	184	165
65°	142	141
75°	90	94
85°	24	28
90°	0	



TEST NUMBER: P794530

CATALOG NUMBER: LER6D60D010-EC6DR6055659040-6LBDP1MW

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	8168.7
2.5°	8398.3
5°	8337.7
7.5°	8356.8
10°	8341.9
12.5°	8169.7
15°	7794.5
17.5°	7290.6
20°	6685.7
22.5°	6038.3
25°	5215.4
27.5°	4171.5
30°	3371.0
32.5°	2598.2
35°	1597.8
37.5°	683.6
40°	242.4
42.5°	223.2
45°	219.0
47.5°	211.6
50°	203.0
52.5°	193.5
55°	183.9
57.5°	174.3
60°	164.8
62.5°	154.1
65°	142.5
67.5°	130.8
70°	118.0
72.5°	104.2
75°	90.4
77.5°	74.4
80°	58.5
82.5°	41.5
85°	24.5
87.5°	8.5
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)