

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P794543

Luminaire Tested: LER6D60D010-EC6DR6555659024-6LBDP1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P794543
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D60D010-EC6DR6555659024-6LBDP1B
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4004.5 lumens
Efficiency: N/A
Efficacy: 62.2 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 64.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P794543
CATALOG NUMBER: LER6D60D010-EC6DR6555659024-6LBDP1B

Luminous Intensity Polar Plot





TEST NUMBER: P794543

CATALOG NUMBER: LER6D60D010-EC6DR6555659024-6LBDP1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93																			
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87																			
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80																			
4	97	89	84	79	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	83	78	73	90	83	77	73	81	76	72	79	75	72	77	74	71	69																			
6	87	78	72	68	86	77	72	68	76	71	67	74	70	67	73	69	66	65																			
7	83	73	67	63	81	73	67	63	71	66	62	70	66	62	69	65	62	60																			
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	57																			
9	75	65	59	55	74	65	59	55	64	58	55	63	58	55	62	58	54	53																			
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	430782
5°	431145
10°	446315
15°	447053
20°	411594
25°	350697
30°	268476
35°	189670
40°	111964
45°	45444
50°	16471
55°	9182
60°	5266
65°	2896
70°	3035
75°	2364
80°	2454
85°	2131

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 45444 cd/sqm



TEST NUMBER: P794543

CATALOG NUMBER: LER6D60D010-EC6DR6555659024-6LBDP1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	379.6	9.5
10°-20°	1095.1	27.3
20°-30°	1313.9	32.8
30°-40°	883.0	22.1
40°-50°	264.3	6.6
50°-60°	46.6	1.2
60°-70°	13.3	0.3
70°-80°	6.5	0.2
80°-90°	2.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2788.7	69.6
0°-40°	3671.7	91.7
0°-60°	3982.7	99.5
0°-90°	4004.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4004.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3943	
5°	3931	380
15°	3952	1095
25°	2909	1314
35°	1422	883
45°	294	264
55°	48	47
65°	11	13
75°	6	6
85°	2	2
90°	0	



TEST NUMBER: P794543

CATALOG NUMBER: LER6D60D010-EC6DR6555659024-6LBDP1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	3942.7
2.5°	3959.5
5°	3931.0
7.5°	3990.3
10°	4022.8
12.5°	4015.0
15°	3952.2
17.5°	3798.7
20°	3539.9
22.5°	3235.1
25°	2909.0
27.5°	2540.9
30°	2128.0
32.5°	1753.7
35°	1422.0
37.5°	1094.2
40°	785.0
42.5°	512.7
45°	294.1
47.5°	155.8
50°	96.9
52.5°	67.2
55°	48.2
57.5°	34.7
60°	24.1
62.5°	15.7
65°	11.2
67.5°	10.1
70°	9.5
72.5°	7.3
75°	5.6
77.5°	5.0
80°	3.9
82.5°	2.8
85°	1.7
87.5°	1.1
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)