

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204452

Luminaire Tested: **LSR6B10D010BZ EC6B10209030 6LBSB1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P204452  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSR6B10D010BZ EC6B10209030 6LBSB1  
Description: PORTFOLIO 6IN CYLINDER  
SHALLOW DISTRIBUTION WITH SPECULAR BLACK TRIM  
WATTAGE D010TR-10.05 W DE010-10.58 W D5LT-10.2 W DMX-10.6 W DL2-11.8 W  
DL3-11.1 W DLE-11.39 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 831.0 lumens  
Efficiency: N/A  
Efficacy: 83.9 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.3  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 9.9  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P204452

CATALOG NUMBER: LSR6B10D010BZ EC6B10209030 6LBSB1

### Luminous Intensity Polar Plot





TEST NUMBER: P204452

CATALOG NUMBER: LSR6B10D010BZ EC6B10209030 6LBSB1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	111	107	103	100	108	105	101	98	100	98	95	97	94	93	93	91	90	88			88																
2	102	95	89	84	100	93	88	83	90	85	81	86	83	79	84	80	78	76			76																
3	94	84	77	72	91	83	76	71	80	74	70	77	73	68	75	71	67	65			65																
4	86	76	68	62	84	74	67	61	72	65	60	70	64	60	68	63	59	57			57																
5	80	68	60	54	78	67	59	53	65	58	53	63	57	52	61	56	52	50			50																
6	74	62	53	47	72	61	53	47	59	52	47	57	51	46	56	50	46	44			44																
7	69	56	48	42	67	55	48	42	54	47	42	52	46	41	51	45	41	39			39																
8	64	51	43	38	63	51	43	38	49	42	37	48	42	37	47	41	37	35			35																
9	60	47	39	34	59	47	39	34	46	39	34	45	38	34	44	38	34	32			32																
10	56	44	36	31	55	43	36	31	42	36	31	41	35	31	40	35	31	29			29																

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P204452

CATALOG NUMBER: LSR6B10D010BZ EC6B10209030 6LBSB1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	34.6	4.2
10°-20°	98.2	11.8
20°-30°	146.0	17.6
30°-40°	169.9	20.4
40°-50°	165.7	19.9
50°-60°	127.4	15.3
60°-70°	70.4	8.5
70°-80°	18.7	2.2
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	278.8	33.6
0°-40°	448.8	54.0
0°-60°	741.8	89.3
0°-90°	831.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	831.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	367	
5°	364	35
15°	348	98
25°	317	146
35°	273	170
45°	215	166
55°	142	127
65°	71	70
75°	16	19
85°	0	0
90°	0	



TEST NUMBER: P204452

CATALOG NUMBER: LSR6B10D010BZ EC6B10209030 6LBSB1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	366.6
2.5°	366.6
5°	364.5
7.5°	361.3
10°	359.2
12.5°	352.9
15°	347.6
17.5°	342.4
20°	335.0
22.5°	327.6
25°	317.1
27.5°	306.6
30°	296.0
32.5°	284.4
35°	272.8
37.5°	258.1
40°	245.5
42.5°	231.8
45°	214.9
47.5°	199.1
50°	181.2
52.5°	162.2
55°	142.2
57.5°	123.3
60°	105.3
62.5°	87.4
65°	70.6
67.5°	54.8
70°	40.0
72.5°	27.4
75°	15.8
77.5°	7.4
80°	1.1
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)