

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P794573

Luminaire Tested: LER6D60D010-EC6DR6555659035-6LBS1LI

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P794573  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LER6D60D010-EC6DR6555659035-6LBS1LI  
Description: 6 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 65° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7007.3 lumens  
Efficiency: N/A  
Efficacy: 108.8 lumens/watt  
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96  
Luminous Opening: Circular (Dia: 0.48' x H: 0')  
CIE Type: Direct

Input Watts (W): 64.4  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight

TEST NUMBER: P794573

CATALOG NUMBER: LER6D60D010-EC6DR6555659035-6LBS1LI

### Luminous Intensity Polar Plot





TEST NUMBER: P794573  
 CATALOG NUMBER: LER6D60D010-EC6DR6555659035-6LBS1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10		0		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93			
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85			
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78			
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72			
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66			
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61			
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56			
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52			
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49			
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	371589
5°	370651
10°	370335
15°	358921
20°	326752
25°	284741
30°	236825
35°	187649
40°	135434
45°	85561
50°	44603
55°	23705
60°	12452
65°	6854
70°	2869
75°	3159
80°	2186
85°	1876

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 85561 cd/sqm



TEST NUMBER: P794573

CATALOG NUMBER: LER6D60D010-EC6DR6555659035-6LBS1LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	601.7	8.6
10°-20°	1647.6	23.5
20°-30°	2014.0	28.7
30°-40°	1634.1	23.3
40°-50°	814.3	11.6
50°-60°	227.1	3.2
60°-70°	51.6	0.7
70°-80°	13.4	0.2
80°-90°	3.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4263.3	60.8
0°-40°	5897.3	84.2
0°-60°	6938.8	99.0
0°-90°	7007.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7007.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	6362	
5°	6322	602
15°	5936	1648
25°	4419	2014
35°	2632	1634
45°	1036	814
55°	233	227
65°	50	52
75°	14	13
85°	3	3
90°	0	



TEST NUMBER: P794573

CATALOG NUMBER: LER6D60D010-EC6DR6555659035-6LBS1LI

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	6362.4
2.5°	6357.7
5°	6322.2
7.5°	6301.6
10°	6244.6
12.5°	6128.7
15°	5936.1
17.5°	5635.0
20°	5257.3
22.5°	4849.6
25°	4418.6
27.5°	3957.7
30°	3511.7
32.5°	3071.3
35°	2631.9
37.5°	2193.4
40°	1776.4
42.5°	1385.6
45°	1035.9
47.5°	721.8
50°	490.9
52.5°	338.5
55°	232.8
57.5°	157.1
60°	106.6
62.5°	73.9
65°	49.6
67.5°	25.2
70°	16.8
72.5°	15.9
75°	14.0
77.5°	9.3
80°	6.5
82.5°	4.7
85°	2.8
87.5°	1.9
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)