

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P205076

Luminaire Tested: **LSR6B10D010BZ EC6B10209730 6LBMLI1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P205076
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR6B10D010BZ EC6B10209730 6LBMLI1
Description: PORTFOLIO 6IN CYLINDER
MEDIUM DISTRIBUTION WITH SPECULAR CLEAR TRIM
WATTAGE D010TR-10.05 W DE010-10.58 W D5LT-10.2 W DMX-10.6 W DL2-11.8 W
DL3-11.1 W DLE-11.39 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 709.8 lumens
Efficiency: N/A
Efficacy: 71.7 lumens/watt
Spacing Criteria (0/90/45): 0.85 / 0.85 / 0.85
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P205076

CATALOG NUMBER: LSR6B10D010BZ EC6B10209730 6LBML11

Luminous Intensity Polar Plot





TEST NUMBER: P205076

CATALOG NUMBER: LSR6B10D010BZ EC6B10209730 6LBML11

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																			
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																												
1	114	111	109	106	111	109	107	105	105	103	101	101	100	98	98	97	96	94																												
2	108	103	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88																												
3	103	97	92	88	101	95	91	87	93	89	86	90	87	85	88	85	83	82																												
4	98	91	85	81	96	89	84	81	87	83	80	85	82	79	83	80	78	76																												
5	93	85	79	75	91	84	79	75	82	78	74	81	77	73	79	76	73	71																												
6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	68	67																												
7	84	75	69	65	83	75	69	65	73	68	65	72	68	64	71	67	64	63																												
8	80	71	65	61	79	70	65	61	69	64	61	68	64	60	67	63	60	59																												
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55																												
10	73	64	58	54	72	63	58	54	62	57	54	62	57	54	61	57	54	52																												

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P205076

CATALOG NUMBER: LSR6B10D010BZ EC6B10209730 6LBML11

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	81.8	11.5
10°-20°	203.7	28.7
20°-30°	236.8	33.4
30°-40°	145.0	20.4
40°-50°	36.0	5.1
50°-60°	4.2	0.6
60°-70°	1.6	0.2
70°-80°	0.6	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	522.4	73.6
0°-40°	667.4	94.0
0°-60°	707.6	99.7
0°-90°	709.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	709.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	888	
5°	876	82
15°	731	204
25°	524	237
35°	227	145
45°	40	36
55°	4	4
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P205076

CATALOG NUMBER: LSR6B10D010BZ EC6B10209730 6LBML11

CANDELA DISTRIBUTION (FULL):

0°	
0°	888.3
2.5°	887.4
5°	876.5
7.5°	852.9
10°	821.1
12.5°	779.3
15°	731.2
17.5°	679.4
20°	628.5
22.5°	577.7
25°	524.1
27.5°	462.3
30°	391.5
32.5°	308.8
35°	227.1
37.5°	159.9
40°	109.0
42.5°	68.1
45°	40.0
47.5°	22.7
50°	11.8
52.5°	5.4
55°	3.6
57.5°	2.7
60°	2.7
62.5°	1.8
65°	1.8
67.5°	0.9
70°	0.9
72.5°	0.9
75°	0.9
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)