

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P794581

Luminaire Tested: LER6D60D010-EC6DR6555659040-6LBS1LI

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P794581  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LER6D60D010-EC6DR6555659040-6LBS1LI  
Description: 6 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 65° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7334.9 lumens  
Efficiency: N/A  
Efficacy: 113.9 lumens/watt  
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96  
Luminous Opening: Circular (Dia: 0.48' x H: 0')  
CIE Type: Direct

Input Watts (W): 64.4  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight

TEST NUMBER: P794581

CATALOG NUMBER: LER6D60D010-EC6DR6555659040-6LBS1LI

### Luminous Intensity Polar Plot





TEST NUMBER: P794581  
 CATALOG NUMBER: LER6D60D010-EC6DR6555659040-6LBS1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93	93	93	93
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85	85	85	85
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78	78	78	78
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72	72	72	72
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66	66	66	66
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61	61	61	61
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56	56	56	56
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52	52	52	52
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49	49	49	49
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46	46	46	46

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	388964
5°	387982
10°	387652
15°	375700
20°	342029
25°	298055
30°	247899
35°	196426
40°	141770
45°	89567
50°	46684
55°	24815
60°	13036
65°	7172
70°	3005
75°	3317
80°	2321
85°	1943

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 89567 cd/sqm



TEST NUMBER: P794581

CATALOG NUMBER: LER6D60D010-EC6DR6555659040-6LBS1LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	629.8	8.6
10°-20°	1724.7	23.5
20°-30°	2108.1	28.7
30°-40°	1710.5	23.3
40°-50°	852.4	11.6
50°-60°	237.7	3.2
60°-70°	54.0	0.7
70°-80°	14.1	0.2
80°-90°	3.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4462.6	60.8
0°-40°	6173.1	84.2
0°-60°	7263.2	99.0
0°-90°	7334.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7334.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	6660	
5°	6618	630
15°	6214	1725
25°	4625	2108
35°	2755	1710
45°	1084	852
55°	244	238
65°	52	54
75°	15	14
85°	3	4
90°	0	



TEST NUMBER: P794581

CATALOG NUMBER: LER6D60D010-EC6DR6555659040-6LBS1LI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	6659.9
2.5°	6655.0
5°	6617.8
7.5°	6596.3
10°	6536.6
12.5°	6415.2
15°	6213.6
17.5°	5898.5
20°	5503.1
22.5°	5076.4
25°	4625.2
27.5°	4142.7
30°	3675.9
32.5°	3214.9
35°	2755.0
37.5°	2296.0
40°	1859.5
42.5°	1450.4
45°	1084.4
47.5°	755.5
50°	513.8
52.5°	354.3
55°	243.7
57.5°	164.4
60°	111.6
62.5°	77.3
65°	51.9
67.5°	26.4
70°	17.6
72.5°	16.6
75°	14.7
77.5°	9.8
80°	6.9
82.5°	4.9
85°	2.9
87.5°	2.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)