

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P202604

Luminaire Tested: **LSR6B10D010BZ EC6B10209730 6LBMWMH1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P202604  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSR6B10D010BZ EC6B10209730 6LBMWMH1  
Description: PORTFOLIO 6IN CYLINDER  
MEDIUM DISTRIBUTION WITH WARM HAZE TRIM  
WATTAGE D010TR-10.05 W DE010-10.58 W D5LT-10.2 W DMX-10.6 W DL2-11.8 W  
DL3-11.1 W DLE-11.39 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 622.3 lumens  
Efficiency: N/A  
Efficacy: 62.9 lumens/watt  
Spacing Criteria (0/90/45): 0.9 / 0.9 / 0.89  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 9.9  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P202604

CATALOG NUMBER: LSR6B10D010BZ EC6B10209730 6LBMWMH1

### Luminous Intensity Polar Plot





TEST NUMBER: P202604

CATALOG NUMBER: LSR6B10D010BZ EC6B10209730 6LBMWMH1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93																			
2	108	103	99	95	105	101	97	94	98	95	92	95	92	90	92	90	88	86																			
3	102	95	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80																			
4	97	89	83	79	95	88	83	79	86	81	78	84	80	77	82	79	76	74																			
5	92	83	77	73	90	82	77	73	80	76	72	79	75	71	77	74	71	69																			
6	87	78	72	67	85	77	71	67	76	71	67	74	70	66	73	69	66	64																			
7	83	73	67	63	81	72	67	63	71	66	62	70	65	62	69	65	61	60																			
8	78	69	63	58	77	68	62	58	67	62	58	66	61	58	65	61	58	56																			
9	75	65	59	55	73	64	59	55	63	58	54	62	58	54	62	57	54	53																			
10	71	61	55	51	70	61	55	51	60	55	51	59	54	51	58	54	51	50																			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P202604

CATALOG NUMBER: LSR6B10D010BZ EC6B10209730 6LBMWMH1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	63.5	10.2
10°-20°	163.1	26.2
20°-30°	200.3	32.2
30°-40°	137.3	22.1
40°-50°	44.1	7.1
50°-60°	9.0	1.4
60°-70°	3.5	0.6
70°-80°	1.3	0.2
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	426.9	68.6
0°-40°	564.2	90.7
0°-60°	617.3	99.2
0°-90°	622.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	622.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	692	
5°	679	64
15°	583	163
25°	442	200
35°	219	137
45°	52	44
55°	9	9
65°	4	4
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P202604

CATALOG NUMBER: LSR6B10D010BZ EC6B10209730 6LBMWMH1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	692.1
2.5°	687.9
5°	678.9
7.5°	662.0
10°	639.3
12.5°	611.3
15°	583.3
17.5°	552.2
20°	517.9
22.5°	482.0
25°	441.9
27.5°	397.5
30°	341.6
32.5°	279.8
35°	219.1
37.5°	163.6
40°	117.7
42.5°	80.2
45°	52.3
47.5°	32.2
50°	19.5
52.5°	12.1
55°	9.0
57.5°	6.9
60°	5.3
62.5°	4.2
65°	3.7
67.5°	2.6
70°	2.1
72.5°	1.6
75°	1.1
77.5°	1.1
80°	0.5
82.5°	0.5
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)