

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204140

Luminaire Tested: **LSR6B10D010BZ EC6B10208040 6LBSH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204140
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR6B10D010BZ EC6B10208040 6LBSH1
Description: PORTFOLIO 6IN CYLINDER
SHALLOW DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
WATTAGE D010TR-10.05 W DE010-10.58 W D5LT-10.2 W DMX-10.6 W DL2-11.8 W
DL3-11.1 W DLE-11.39 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1146.8 lumens
Efficiency: N/A
Efficacy: 115.8 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204140

CATALOG NUMBER: LSR6B10D010BZ EC6B10208040 6LBSH1

Luminous Intensity Polar Plot





TEST NUMBER: P204140

CATALOG NUMBER: LSR6B10D010BZ EC6B10208040 6LBSH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	102	96	90	85	100	94	88	84	90	86	82	87	83	80	84	81	79	77			
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67			
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58			
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51			
6	75	63	55	49	73	62	54	49	60	54	49	59	53	48	57	52	48	46			
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41			
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37			
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34			
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204140

CATALOG NUMBER: LSR6B10D010BZ EC6B10208040 6LBSH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	56.2	4.9
10°-20°	152.7	13.3
20°-30°	212.1	18.5
30°-40°	231.4	20.2
40°-50°	215.9	18.8
50°-60°	163.8	14.3
60°-70°	89.7	7.8
70°-80°	24.7	2.2
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	420.9	36.7
0°-40°	652.3	56.9
0°-60°	1032.0	90.0
0°-90°	1146.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1146.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	600	
5°	595	56
15°	544	153
25°	461	212
35°	370	231
45°	280	216
55°	183	164
65°	90	90
75°	22	25
85°	0	0
90°	0	



TEST NUMBER: P204140

CATALOG NUMBER: LSR6B10D010BZ EC6B10208040 6LBSH1

CANDELA DISTRIBUTION (FULL):

0°	
0°	599.8
2.5°	599.8
5°	594.7
7.5°	587.2
10°	575.8
12.5°	560.6
15°	544.2
17.5°	524.0
20°	505.1
22.5°	482.4
25°	460.9
27.5°	439.4
30°	415.4
32.5°	392.7
35°	370.0
37.5°	347.2
40°	325.8
42.5°	303.0
45°	280.3
47.5°	257.6
50°	232.3
52.5°	208.3
55°	183.1
57.5°	159.1
60°	135.1
62.5°	111.1
65°	89.7
67.5°	69.4
70°	51.8
72.5°	35.4
75°	21.5
77.5°	10.1
80°	2.5
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)