

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P794617

Luminaire Tested: LER6D60D010-EC6DR7055659035-6LBDP1LI

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P794617
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D60D010-EC6DR7055659035-6LB DP1LI
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7668.6 lumens
Efficiency: N/A
Efficacy: 119.1 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 64.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P794617
CATALOG NUMBER: LER6D60D010-EC6DR7055659035-6LBDP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P794617

CATALOG NUMBER: LER6D60D010-EC6DR7055659035-6LBDP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	942013
5°	914014
10°	888547
15°	876879
20°	818828
25°	615149
30°	434860
35°	154030
40°	80999
45°	86267
50°	89324
55°	91016
60°	91582
65°	89633
70°	84592
75°	78351
80°	69590
85°	56413

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 91610 cd/sqm



TEST NUMBER: P794617

CATALOG NUMBER: LER6D60D010-EC6DR7055659035-6LBDP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	786.0	10.3
10°-20°	2156.1	28.1
20°-30°	2374.6	31.0
30°-40°	907.3	11.8
40°-50°	428.4	5.6
50°-60°	425.9	5.6
60°-70°	341.0	4.4
70°-80°	196.0	2.6
80°-90°	53.3	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5316.8	69.3
0°-40°	6224.0	81.2
0°-60°	7078.3	92.3
0°-90°	7668.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7668.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8622	
5°	8334	786
15°	7752	2156
25°	5103	2375
35°	1155	907
45°	558	428
55°	478	426
65°	347	341
75°	186	196
85°	45	53
90°	0	



TEST NUMBER: P794617

CATALOG NUMBER: LER6D60D010-EC6DR7055659035-6LBDP1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	8621.7
2.5°	8531.6
5°	8333.6
7.5°	8168.5
10°	8008.8
12.5°	7873.6
15°	7752.1
17.5°	7458.7
20°	7042.3
22.5°	6144.1
25°	5102.6
27.5°	4441.9
30°	3446.8
32.5°	2226.4
35°	1154.8
37.5°	623.8
40°	567.9
42.5°	563.8
45°	558.3
47.5°	546.0
50°	525.5
52.5°	502.3
55°	477.8
57.5°	450.5
60°	419.1
62.5°	383.6
65°	346.7
67.5°	305.8
70°	264.8
72.5°	223.9
75°	185.6
77.5°	146.1
80°	110.6
82.5°	77.8
85°	45.0
87.5°	17.7
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)