

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204662

Luminaire Tested: **LSR6B10D010BZ EC6B10209040 6LBPSMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204662
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR6B10D010BZ EC6B10209040 6LBPSMW1
Description: PORTFOLIO 6IN CYLINDER
SHALLOW DISTRIBUTION WITH PLASTIC MATTE WHITE TRIM
WATTAGE D010TR-10.05 W DE010-10.58 W D5LT-10.2 W DMX-10.6 W DL2-11.8 W
DL3-11.1 W DLE-11.39 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1001.6 lumens
Efficiency: N/A
Efficacy: 101.2 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.34
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204662

CATALOG NUMBER: LSR6B10D010BZ EC6B10209040 6LBPSMW1

Luminous Intensity Polar Plot





TEST NUMBER: P204662

CATALOG NUMBER: LSR6B10D010BZ EC6B10209040 6LBPSMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	110	106	102	99	107	104	100	97	99	97	94	96	93	91	92	90	88	86																			
2	101	93	87	82	98	92	86	81	88	83	79	85	81	77	82	79	76	74																			
3	93	83	75	69	90	81	74	69	78	72	67	76	70	66	73	69	65	63																			
4	85	74	66	59	83	72	65	59	70	63	58	68	62	57	66	61	56	54																			
5	78	66	58	51	76	65	57	51	63	56	51	61	55	50	59	54	49	47																			
6	73	60	51	45	71	59	51	45	57	50	44	55	49	44	54	48	44	42																			
7	67	54	46	40	66	54	46	40	52	45	40	51	44	39	49	43	39	37																			
8	63	50	41	36	61	49	41	36	48	41	35	46	40	35	45	39	35	33																			
9	59	46	38	32	57	45	37	32	44	37	32	43	36	32	42	36	32	30																			
10	55	42	34	29	54	42	34	29	41	34	29	40	33	29	39	33	29	27																			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204662

CATALOG NUMBER: LSR6B10D010BZ EC6B10209040 6LBPSMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	38.2	3.8
10°-20°	109.0	10.9
20°-30°	164.1	16.4
30°-40°	195.3	19.5
40°-50°	195.0	19.5
50°-60°	158.6	15.8
60°-70°	97.5	9.7
70°-80°	37.8	3.8
80°-90°	6.0	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	311.4	31.1
0°-40°	506.7	50.6
0°-60°	860.2	85.9
0°-90°	1001.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1001.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	404	
5°	402	38
15°	387	109
25°	357	164
35°	313	195
45°	253	195
55°	177	159
65°	98	98
75°	34	38
85°	5	6
90°	0	



TEST NUMBER: P204662

CATALOG NUMBER: LSR6B10D010BZ EC6B10209040 6LBPSMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	403.5
2.5°	404.1
5°	402.3
7.5°	400.0
10°	397.0
12.5°	391.7
15°	386.9
17.5°	379.8
20°	372.1
22.5°	365.0
25°	357.2
27.5°	346.6
30°	335.9
32.5°	325.8
35°	312.7
37.5°	298.5
40°	285.4
42.5°	269.4
45°	253.4
47.5°	236.2
50°	217.8
52.5°	198.8
55°	177.4
57.5°	156.7
60°	136.5
62.5°	116.9
65°	97.9
67.5°	80.1
70°	63.5
72.5°	48.1
75°	34.4
77.5°	22.6
80°	13.6
82.5°	8.3
85°	4.7
87.5°	2.4
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)