

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204145

Luminaire Tested: **LSR6B10D010BZ EC6B10209040 6LBSH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204145
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR6B10D010BZ EC6B10209040 6LBSH1
Description: PORTFOLIO 6IN CYLINDER
SHALLOW DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
WATTAGE D010TR-10.05 W DE010-10.58 W D5LT-10.2 W DMX-10.6 W DL2-11.8 W
DL3-11.1 W DLE-11.39 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 960.4 lumens
Efficiency: N/A
Efficacy: 97.0 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204145

CATALOG NUMBER: LSR6B10D010BZ EC6B10209040 6LBSH1

Luminous Intensity Polar Plot





TEST NUMBER: P204145

CATALOG NUMBER: LSR6B10D010BZ EC6B10209040 6LBSH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|---|--|--|--|--|--|--|----|--|--|--|--|--|--|--|--|---|
| RF | 20 | | | | | | | | | 20 | | | | | | | | | 20 | | | | | | | | | 20 | | | | | | | | | |
| RC | 80 | | | | | | | | | 50 | | | | | | | | | 30 | | | | | | | | | 10 | | | | | | | | | 0 |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 | | | | | | | | | | | | | | | | |
| RCR | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | | | | | | | | | | | | | | | | | | |
| 1 | 111 | 107 | 104 | 101 | 108 | 105 | 102 | 99 | 101 | 98 | 96 | 97 | 95 | 93 | 93 | 92 | 90 | 88 | | | | | | | | | | | | | | | | | | | |
| 2 | 102 | 96 | 90 | 85 | 100 | 94 | 88 | 84 | 90 | 86 | 82 | 87 | 83 | 80 | 84 | 81 | 79 | 77 | | | | | | | | | | | | | | | | | | | |
| 3 | 95 | 85 | 78 | 73 | 92 | 84 | 77 | 72 | 81 | 75 | 71 | 78 | 74 | 70 | 76 | 72 | 69 | 67 | | | | | | | | | | | | | | | | | | | |
| 4 | 87 | 77 | 69 | 63 | 85 | 75 | 68 | 63 | 73 | 67 | 62 | 71 | 65 | 61 | 69 | 64 | 60 | 58 | | | | | | | | | | | | | | | | | | | |
| 5 | 81 | 69 | 61 | 55 | 79 | 68 | 61 | 55 | 66 | 60 | 55 | 64 | 59 | 54 | 63 | 58 | 53 | 51 | | | | | | | | | | | | | | | | | | | |
| 6 | 75 | 63 | 55 | 49 | 73 | 62 | 54 | 49 | 60 | 54 | 49 | 59 | 53 | 48 | 57 | 52 | 48 | 46 | | | | | | | | | | | | | | | | | | | |
| 7 | 70 | 58 | 50 | 44 | 68 | 57 | 49 | 44 | 55 | 49 | 44 | 54 | 48 | 43 | 53 | 47 | 43 | 41 | | | | | | | | | | | | | | | | | | | |
| 8 | 65 | 53 | 45 | 40 | 64 | 52 | 45 | 40 | 51 | 44 | 39 | 50 | 44 | 39 | 49 | 43 | 39 | 37 | | | | | | | | | | | | | | | | | | | |
| 9 | 61 | 49 | 41 | 36 | 60 | 48 | 41 | 36 | 47 | 40 | 36 | 46 | 40 | 36 | 45 | 40 | 35 | 34 | | | | | | | | | | | | | | | | | | | |
| 10 | 58 | 45 | 38 | 33 | 56 | 45 | 38 | 33 | 44 | 37 | 33 | 43 | 37 | 33 | 42 | 37 | 33 | 31 | | | | | | | | | | | | | | | | | | | |

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204145

CATALOG NUMBER: LSR6B10D010BZ EC6B10209040 6LBSH1

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 47.0 | 4.9 |
| 10°-20° | 127.9 | 13.3 |
| 20°-30° | 177.6 | 18.5 |
| 30°-40° | 193.8 | 20.2 |
| 40°-50° | 180.8 | 18.8 |
| 50°-60° | 137.2 | 14.3 |
| 60°-70° | 75.2 | 7.8 |
| 70°-80° | 20.7 | 2.2 |
| 80°-90° | 0.3 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 352.5 | 36.7 |
| 0°-40° | 546.3 | 56.9 |
| 0°-60° | 864.3 | 90.0 |
| 0°-90° | 960.4 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 960.4 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|-----|------|
| 0° | 502 | |
| 5° | 498 | 47 |
| 15° | 456 | 128 |
| 25° | 386 | 178 |
| 35° | 310 | 194 |
| 45° | 235 | 181 |
| 55° | 153 | 137 |
| 65° | 75 | 75 |
| 75° | 18 | 21 |
| 85° | 0 | 0 |
| 90° | 0 | |



TEST NUMBER: P204145

CATALOG NUMBER: LSR6B10D010BZ EC6B10209040 6LBSH1

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|-------|
| 0° | 502.3 |
| 2.5° | 502.3 |
| 5° | 498.0 |
| 7.5° | 491.7 |
| 10° | 482.2 |
| 12.5° | 469.5 |
| 15° | 455.7 |
| 17.5° | 438.8 |
| 20° | 423.0 |
| 22.5° | 403.9 |
| 25° | 386.0 |
| 27.5° | 368.0 |
| 30° | 347.9 |
| 32.5° | 328.9 |
| 35° | 309.8 |
| 37.5° | 290.8 |
| 40° | 272.8 |
| 42.5° | 253.8 |
| 45° | 234.7 |
| 47.5° | 215.7 |
| 50° | 194.6 |
| 52.5° | 174.5 |
| 55° | 153.3 |
| 57.5° | 133.2 |
| 60° | 113.1 |
| 62.5° | 93.1 |
| 65° | 75.1 |
| 67.5° | 58.2 |
| 70° | 43.4 |
| 72.5° | 29.6 |
| 75° | 18.0 |
| 77.5° | 8.5 |
| 80° | 2.1 |
| 82.5° | 0.0 |
| 85° | 0.0 |
| 87.5° | 0.0 |
| 90° | 0.0 |



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)