

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P794634

Luminaire Tested: LER6D60D010-EC6DR7055659050-6LBDP1MW

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P794634
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D60D010-EC6DR7055659050-6LB DP1MW
Description: 6 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6014.0 lumens
Efficiency: N/A
Efficacy: 93.4 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 64.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P794634

CATALOG NUMBER: LER6D60D010-EC6DR7055659050-6LBDP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P794634

CATALOG NUMBER: LER6D60D010-EC6DR7055659050-6LBDP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	738767
5°	716812
10°	696831
15°	687683
20°	642163
25°	482417
30°	341032
35°	120805
40°	63513
45°	67648
50°	70066
55°	71377
60°	71828
65°	70295
70°	66351
75°	61465
80°	54552
85°	44253

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 71844 cd/sqm



TEST NUMBER: P794634

CATALOG NUMBER: LER6D60D010-EC6DR7055659050-6LBDP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	616.4	10.3
10°-20°	1690.9	28.1
20°-30°	1862.3	31.0
30°-40°	711.5	11.8
40°-50°	335.9	5.6
50°-60°	334.0	5.6
60°-70°	267.4	4.4
70°-80°	153.7	2.6
80°-90°	41.8	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4169.6	69.3
0°-40°	4881.1	81.2
0°-60°	5551.1	92.3
0°-90°	6014.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6014.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6762	
5°	6536	616
15°	6080	1691
25°	4002	1862
35°	906	712
45°	438	336
55°	375	334
65°	272	267
75°	146	154
85°	35	42
90°	0	



TEST NUMBER: P794634

CATALOG NUMBER: LER6D60D010-EC6DR7055659050-6LBDP1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	6761.5
2.5°	6690.8
5°	6535.6
7.5°	6406.0
10°	6280.8
12.5°	6174.8
15°	6079.5
17.5°	5849.4
20°	5522.9
22.5°	4818.4
25°	4001.6
27.5°	3483.5
30°	2703.1
32.5°	1746.0
35°	905.7
37.5°	489.2
40°	445.3
42.5°	442.1
45°	437.8
47.5°	428.2
50°	412.2
52.5°	394.0
55°	374.7
57.5°	353.3
60°	328.7
62.5°	300.8
65°	271.9
67.5°	239.8
70°	207.7
72.5°	175.6
75°	145.6
77.5°	114.5
80°	86.7
82.5°	61.0
85°	35.3
87.5°	13.9
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)