

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203832

Luminaire Tested: **LSR6B10D010BZ EC6B10208050 6LBNGPH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203832
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR6B10D010BZ EC6B10208050 6LBNGPH1
Description: PORTFOLIO 6IN CYLINDER
NARROW DISTRIBUTION WITH GRAPHITE HAZE TRIM
WATTAGE D010TR-10.05 W DE010-10.58 W D5LT-10.2 W DMX-10.6 W DL2-11.8 W
DL3-11.1 W DLE-11.39 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 553.9 lumens
Efficiency: N/A
Efficacy: 55.9 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.88
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203832

CATALOG NUMBER: LSR6B10D010BZ EC6B10208050 6LBNGPH1

Luminous Intensity Polar Plot





TEST NUMBER: P203832

CATALOG NUMBER: LSR6B10D010BZ EC6B10208050 6LBNGPH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20																	
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																								
RCR																																																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																																				
1	114	111	108	106	111	109	106	104	105	103	101	101	100	98	97	96	95	94																																				
2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	92	91	89	87																																				
3	103	96	91	87	101	95	90	87	92	88	85	90	87	84	88	85	83	81																																				
4	97	90	84	80	96	89	84	80	87	82	79	85	81	78	83	80	77	76																																				
5	93	84	78	74	91	83	78	74	82	77	73	80	76	73	78	75	72	70																																				
6	88	79	73	69	86	78	73	69	77	72	68	75	71	68	74	70	67	66																																				
7	84	74	68	64	82	74	68	64	72	67	64	71	67	63	70	66	63	62																																				
8	79	70	64	60	78	69	64	60	68	63	60	67	63	59	66	62	59	58																																				
9	76	66	60	56	75	66	60	56	65	60	56	64	59	56	63	59	56	54																																				
10	72	63	57	53	71	62	57	53	61	56	53	61	56	53	60	55	52	51																																				

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203832

CATALOG NUMBER: LSR6B10D010BZ EC6B10208050 6LBNGPH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	60.9	11.0
10°-20°	150.3	27.1
20°-30°	182.1	32.9
30°-40°	124.1	22.4
40°-50°	29.6	5.3
50°-60°	4.6	0.8
60°-70°	1.7	0.3
70°-80°	0.5	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	393.4	71.0
0°-40°	517.5	93.4
0°-60°	551.7	99.6
0°-90°	553.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	553.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	673	
5°	654	61
15°	538	150
25°	398	182
35°	198	124
45°	32	30
55°	5	5
65°	1	2
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P203832

CATALOG NUMBER: LSR6B10D010BZ EC6B10208050 6LBNGPH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	673.2
2.5°	669.4
5°	654.3
7.5°	634.1
10°	605.0
12.5°	572.2
15°	538.1
17.5°	502.7
20°	467.3
22.5°	432.0
25°	397.9
27.5°	366.3
30°	320.8
32.5°	261.5
35°	198.3
37.5°	141.5
40°	93.5
42.5°	58.1
45°	31.6
47.5°	16.4
50°	8.8
52.5°	6.3
55°	5.1
57.5°	3.8
60°	2.5
62.5°	2.5
65°	1.3
67.5°	1.3
70°	1.3
72.5°	1.3
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)