

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204553

Luminaire Tested: **LSR6B10D010BZ EC6B10208050 6LBSMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204553
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR6B10D010BZ EC6B10208050 6LBSMW1
Description: PORTFOLIO 6IN CYLINDER
SHALLOW DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-10.05 W DE010-10.58 W D5LT-10.2 W DMX-10.6 W DL2-11.8 W
DL3-11.1 W DLE-11.39 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1196.0 lumens
Efficiency: N/A
Efficacy: 120.8 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.34
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204553

CATALOG NUMBER: LSR6B10D010BZ EC6B10208050 6LBSMW1

Luminous Intensity Polar Plot





TEST NUMBER: P204553

CATALOG NUMBER: LSR6B10D010BZ EC6B10208050 6LBSMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	110	106	102	99	107	104	100	97	99	97	94	96	93	91	92	90	88	86																			
2	101	93	87	82	98	92	86	81	88	83	79	85	81	77	82	79	76	74																			
3	93	83	75	69	90	81	74	69	78	72	67	76	70	66	73	69	65	63																			
4	85	74	66	59	83	72	65	59	70	63	58	68	62	57	66	61	56	54																			
5	78	66	58	51	76	65	57	51	63	56	51	61	55	50	59	54	49	47																			
6	73	60	51	45	71	59	51	45	57	50	44	55	49	44	54	48	44	42																			
7	67	54	46	40	66	54	46	40	52	45	40	51	44	39	49	43	39	37																			
8	63	50	41	36	61	49	41	36	48	41	35	46	40	35	45	39	35	33																			
9	59	46	38	32	57	45	37	32	44	37	32	43	36	32	42	36	32	30																			
10	55	42	34	29	54	42	34	29	41	34	29	40	33	29	39	33	29	27																			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204553

CATALOG NUMBER: LSR6B10D010BZ EC6B10208050 6LBSMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	45.7	3.8
10°-20°	130.1	10.9
20°-30°	196.0	16.4
30°-40°	233.2	19.5
40°-50°	232.8	19.5
50°-60°	189.3	15.8
60°-70°	116.5	9.7
70°-80°	45.1	3.8
80°-90°	7.2	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	371.8	31.1
0°-40°	605.0	50.6
0°-60°	1027.2	85.9
0°-90°	1196.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1196.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	482	
5°	480	46
15°	462	130
25°	427	196
35°	373	233
45°	303	233
55°	212	189
65°	117	116
75°	41	45
85°	6	7
90°	0	



TEST NUMBER: P204553

CATALOG NUMBER: LSR6B10D010BZ EC6B10208050 6LBSMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	481.9
2.5°	482.6
5°	480.5
7.5°	477.6
10°	474.1
12.5°	467.7
15°	462.0
17.5°	453.5
20°	444.3
22.5°	435.8
25°	426.6
27.5°	413.8
30°	401.1
32.5°	389.0
35°	373.4
37.5°	356.4
40°	340.9
42.5°	321.7
45°	302.6
47.5°	282.0
50°	260.1
52.5°	237.4
55°	211.9
57.5°	187.1
60°	163.0
62.5°	139.6
65°	116.9
67.5°	95.7
70°	75.8
72.5°	57.4
75°	41.1
77.5°	26.9
80°	16.3
82.5°	9.9
85°	5.7
87.5°	2.8
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)