

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P205377

Luminaire Tested: **LSR6B10D010BZ EC6B10209050 6LBSLI1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P205377
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR6B10D010BZ EC6B10209050 6LBSL11
Description: PORTFOLIO 6IN CYLINDER
SHALLOW DISTRIBUTION WITH SPECULAR CLEAR TRIM
WATTAGE D010TR-10.05 W DE010-10.58 W D5LT-10.2 W DMX-10.6 W DL2-11.8 W
DL3-11.1 W DLE-11.39 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 998.5 lumens
Efficiency: N/A
Efficacy: 100.9 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 1.04
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P205377

CATALOG NUMBER: LSR6B10D010BZ EC6B10209050 6LBSLI1

Luminous Intensity Polar Plot





TEST NUMBER: P205377

CATALOG NUMBER: LSR6B10D010BZ EC6B10209050 6LBSLI1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	107	104	101	109	105	102	99	101	99	96	97	95	93	94	92	91	89																			
2	103	96	91	86	100	94	89	85	91	87	83	88	84	81	85	82	79	77																			
3	95	86	79	74	93	85	78	73	82	76	72	79	75	71	77	73	70	68																			
4	88	78	70	64	86	77	69	64	74	68	63	72	67	62	70	65	62	60																			
5	82	71	63	57	80	70	62	57	67	61	56	66	60	55	64	59	55	53																			
6	76	64	56	51	74	63	56	51	62	55	50	60	54	50	59	53	49	47																			
7	71	59	51	46	70	58	51	45	57	50	45	55	49	45	54	49	45	43																			
8	67	54	47	41	65	54	46	41	52	46	41	51	45	41	50	45	41	39																			
9	63	50	43	38	61	50	43	38	49	42	38	48	42	37	47	41	37	36																			
10	59	47	40	35	58	46	39	35	45	39	35	45	39	34	44	38	34	33																			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P205377

CATALOG NUMBER: LSR6B10D010BZ EC6B10209050 6LBSLI1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	58.1	5.8
10°-20°	147.8	14.8
20°-30°	188.5	18.9
30°-40°	195.5	19.6
40°-50°	180.1	18.0
50°-60°	135.5	13.6
60°-70°	73.1	7.3
70°-80°	19.6	2.0
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	394.4	39.5
0°-40°	589.8	59.1
0°-60°	905.5	90.7
0°-90°	998.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	998.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	630	
5°	620	58
15°	527	148
25°	409	188
35°	312	195
45°	234	180
55°	152	135
65°	73	73
75°	17	20
85°	0	0
90°	0	



TEST NUMBER: P205377

CATALOG NUMBER: LSR6B10D010BZ EC6B10209050 6LBSLI1

CANDELA DISTRIBUTION (FULL):

	0°
0°	630.1
2.5°	628.0
5°	620.5
7.5°	606.7
10°	582.4
12.5°	558.0
15°	527.2
17.5°	498.6
20°	468.9
22.5°	438.1
25°	409.4
27.5°	381.9
30°	356.4
32.5°	333.1
35°	311.9
37.5°	291.7
40°	272.6
42.5°	252.5
45°	234.4
47.5°	214.3
50°	194.1
52.5°	172.9
55°	151.7
57.5°	130.5
60°	110.3
62.5°	91.2
65°	73.2
67.5°	56.2
70°	41.4
72.5°	28.6
75°	17.0
77.5°	7.4
80°	2.1
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)