

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203116

Luminaire Tested: **LSR6B10D010BZ EC6B10209050 6LBWMW1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P203116  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSR6B10D010BZ EC6B10209050 6LBWMW1  
Description: PORTFOLIO 6IN CYLINDER  
WIDE DISTRIBUTION WITH MATTE WHITE TRIM  
WATTAGE D010TR-10.05 W DE010-10.58 W D5LT-10.2 W DMX-10.6 W DL2-11.8 W  
DL3-11.1 W DLE-11.39 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 875.4 lumens  
Efficiency: N/A  
Efficacy: 88.4 lumens/watt  
Spacing Criteria (0/90/45): 1.13 / 1.13 / 1.15  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 9.9  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P203116

CATALOG NUMBER: LSR6B10D010BZ EC6B10209050 6LBWMW1

### Luminous Intensity Polar Plot





TEST NUMBER: P203116

CATALOG NUMBER: LSR6B10D010BZ EC6B10209050 6LBWMW1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	100	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	103	96	90	86	100	94	89	85	91	86	83	88	84	81	85	82	79	77			
3	95	86	80	74	93	85	79	74	82	77	72	80	75	71	77	73	70	68			
4	89	78	71	65	86	77	70	65	75	69	64	72	67	63	70	66	62	60			
5	82	71	64	58	80	70	63	58	68	62	57	66	61	56	65	60	56	54			
6	77	65	57	52	75	64	57	52	63	56	51	61	55	51	60	54	50	49			
7	72	60	52	47	70	59	52	47	58	51	46	56	50	46	55	50	46	44			
8	67	55	48	42	66	55	47	42	53	47	42	52	46	42	51	46	42	40			
9	63	51	44	39	62	51	44	39	50	43	39	49	43	38	48	42	38	37			
10	60	48	40	36	58	47	40	36	46	40	36	45	40	35	45	39	35	34			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P203116

CATALOG NUMBER: LSR6B10D010BZ EC6B10209050 6LBWMW1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	46.3	5.3
10°-20°	129.8	14.8
20°-30°	187.1	21.4
30°-40°	194.2	22.2
40°-50°	143.6	16.4
50°-60°	85.8	9.8
60°-70°	52.1	6.0
70°-80°	28.5	3.3
80°-90°	8.0	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	363.2	41.5
0°-40°	557.4	63.7
0°-60°	786.7	89.9
0°-90°	875.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	875.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	492	
5°	488	46
15°	461	130
25°	408	187
35°	313	194
45°	185	144
55°	93	86
65°	52	52
75°	26	29
85°	6	8
90°	0	



TEST NUMBER: P203116

CATALOG NUMBER: LSR6B10D010BZ EC6B10209050 6LBWMW1

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	491.6
2.5°	491.6
5°	488.4
7.5°	484.2
10°	477.8
12.5°	470.4
15°	460.8
17.5°	450.2
20°	439.6
22.5°	424.7
25°	407.7
27.5°	389.7
30°	366.3
32.5°	342.9
35°	313.2
37.5°	282.4
40°	248.4
42.5°	215.5
45°	184.7
47.5°	157.1
50°	132.7
52.5°	111.5
55°	93.4
57.5°	79.6
60°	68.0
62.5°	59.5
65°	52.0
67.5°	45.7
70°	39.3
72.5°	32.9
75°	26.5
77.5°	21.2
80°	15.9
82.5°	11.7
85°	6.4
87.5°	3.2
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)