

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P202807

Luminaire Tested: **LSR6B10D010BZ EC6B10209050 6LBWWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P202807
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR6B10D010BZ EC6B10209050 6LBWWH1
Description: PORTFOLIO 6IN CYLINDER
WIDE DISTRIBUTION WITH WHEAT TRIM
WATTAGE D010TR-10.05 W DE010-10.58 W D5LT-10.2 W DMX-10.6 W DL2-11.8 W
DL3-11.1 W DLE-11.39 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 846.7 lumens
Efficiency: N/A
Efficacy: 85.5 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.18
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P202807

CATALOG NUMBER: LSR6B10D010BZ EC6B10209050 6LBWWH1

Luminous Intensity Polar Plot





TEST NUMBER: P202807

CATALOG NUMBER: LSR6B10D010BZ EC6B10209050 6LBWWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	109	107	104	110	107	105	102	103	101	99	99	98	96	96	95	93	92																			
2	106	100	96	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83																			
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75																			
4	93	84	78	73	91	83	77	72	81	76	71	79	74	71	77	73	70	68																			
5	87	77	71	66	85	76	70	65	75	69	65	73	68	64	71	67	63	62																			
6	82	71	64	59	80	71	64	59	69	63	59	67	62	58	66	61	58	56																			
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51																			
8	72	61	54	49	71	61	54	49	59	53	49	58	53	49	57	52	49	47																			
9	68	57	50	45	67	56	50	45	55	49	45	54	49	45	53	48	45	43																			
10	64	53	46	42	63	53	46	42	52	46	42	51	45	42	50	45	41	40																			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P202807

CATALOG NUMBER: LSR6B10D010BZ EC6B10209050 6LBWWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	50.6	6.0
10°-20°	150.3	17.8
20°-30°	226.3	26.7
30°-40°	231.4	27.3
40°-50°	140.5	16.6
50°-60°	39.6	4.7
60°-70°	6.0	0.7
70°-80°	2.0	0.2
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	427.2	50.4
0°-40°	658.5	77.8
0°-60°	838.6	99.0
0°-90°	846.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	846.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	526	
5°	528	51
15°	532	150
25°	494	226
35°	375	231
45°	181	141
55°	39	40
65°	5	6
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P202807

CATALOG NUMBER: LSR6B10D010BZ EC6B10209050 6LBWWH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	525.9
2.5°	525.9
5°	528.0
7.5°	531.2
10°	531.2
12.5°	533.4
15°	532.3
17.5°	530.2
20°	522.7
22.5°	512.1
25°	494.0
27.5°	473.9
30°	446.2
32.5°	413.3
35°	375.0
37.5°	332.5
40°	283.7
42.5°	232.7
45°	180.6
47.5°	133.9
50°	94.6
52.5°	63.7
55°	39.3
57.5°	23.4
60°	11.7
62.5°	7.4
65°	5.3
67.5°	4.2
70°	3.2
72.5°	2.1
75°	2.1
77.5°	1.1
80°	1.1
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)