

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P795007

Luminaire Tested: LER6D65D010-EC6DR6055659040-6LBDP1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P795007
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D65D010-EC6DR6055659040-6LBDDP1B
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6614.8 lumens
Efficiency: N/A
Efficacy: 90.9 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 72.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P795007
CATALOG NUMBER: LER6D65D010-EC6DR6055659040-6LBDP1B

Luminous Intensity Polar Plot





TEST NUMBER: P795007

CATALOG NUMBER: LER6D65D010-EC6DR6055659040-6LBDP1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93			93																
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86			86																
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80			80																
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75			75																
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70			70																
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66			66																
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62			62																
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59			59																
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55			55																
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53			53																

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	858342
5°	879443
10°	890067
15°	847910
20°	747600
25°	604672
30°	409009
35°	204956
40°	33247
45°	32541
50°	33197
55°	33698
60°	34636
65°	35419
70°	36258
75°	36685
80°	35361
85°	29460

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 75°
 Luminance: 36685 cd/sqm



TEST NUMBER: P795007

CATALOG NUMBER: LER6D65D010-EC6DR6055659040-6LBDP1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	766.4	11.6
10°-20°	2073.4	31.3
20°-30°	2230.9	33.7
30°-40°	969.7	14.7
40°-50°	162.9	2.5
50°-60°	158.4	2.4
60°-70°	135.5	2.0
70°-80°	90.6	1.4
80°-90°	27.1	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5070.6	76.7
0°-40°	6040.4	91.3
0°-60°	6361.6	96.2
0°-90°	6614.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6614.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7856	
5°	8018	766
15°	7496	2073
25°	5016	2231
35°	1537	970
45°	211	163
55°	177	158
65°	137	135
75°	87	91
85°	24	27
90°	0	



TEST NUMBER: P795007

CATALOG NUMBER: LER6D65D010-EC6DR6055659040-6LBDP1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	7855.9
2.5°	8076.7
5°	8018.4
7.5°	8036.8
10°	8022.5
12.5°	7856.9
15°	7496.0
17.5°	7011.4
20°	6429.7
22.5°	5807.1
25°	5015.7
27.5°	4011.8
30°	3241.9
32.5°	2498.7
35°	1536.6
37.5°	657.4
40°	233.1
42.5°	214.7
45°	210.6
47.5°	203.5
50°	195.3
52.5°	186.1
55°	176.9
57.5°	167.7
60°	158.5
62.5°	148.2
65°	137.0
67.5°	125.8
70°	113.5
72.5°	100.2
75°	86.9
77.5°	71.6
80°	56.2
82.5°	39.9
85°	23.5
87.5°	8.2
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)