

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P205279

Luminaire Tested: **LSR6B15D010BZ EC6B10208027 6LBNI1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P205279  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSR6B15D010BZ EC6B10208027 6LBNLI1  
Description: PORTFOLIO 6IN CYLINDER  
NARROW DISTRIBUTION WITH SPECULAR CLEAR TRIM  
WATTAGE D010TR-14.39 W DE010-14.29 W D5LT-14.34 W DMX-14.46 W DL2-15.8 W  
DL3-15.28 W DLE-15.432 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1115.4 lumens  
Efficiency: N/A  
Efficacy: 78.0 lumens/watt  
Spacing Criteria (0/90/45): 0.53 / 0.53 / 0.58  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 14.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P205279

CATALOG NUMBER: LSR6B15D010BZ EC6B10208027 6LBNLI1

### Luminous Intensity Polar Plot





TEST NUMBER: P205279

CATALOG NUMBER: LSR6B15D010BZ EC6B10208027 6LBNLI1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									20									
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																			
RCR	0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100	100	100	100	100	100																			
	1	114	112	109	107	112	109	107	106	105	104	102	102	101	99	98	97	96	95	95	95	95	95	95	95	95	95																			
	2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	89	89	89	89	89	89	89	89	89																			
	3	105	99	94	91	103	97	93	90	95	91	89	93	90	87	90	88	86	85	85	85	85	85	85	85	85	85																			
	4	100	93	88	85	98	92	88	84	90	86	83	88	85	82	86	84	81	80	80	80	80	80	80	80	80	80																			
	5	96	88	83	79	94	87	83	79	86	82	78	84	81	78	83	80	77	76	76	76	76	76	76	76	76	76																			
	6	92	84	79	75	90	83	78	75	82	77	74	80	76	74	79	76	73	72	72	72	72	72	72	72	72	72																			
	7	88	80	74	71	87	79	74	71	78	73	70	77	73	70	76	72	69	68	68	68	68	68	68	68	68	68																			
	8	84	76	71	67	83	75	70	67	74	70	67	73	69	66	73	69	66	65	65	65	65	65	65	65	65	65																			
	9	81	73	67	64	80	72	67	64	71	67	63	70	66	63	70	66	63	62	62	62	62	62	62	62	62	62																			
	10	78	69	64	61	77	69	64	61	68	64	61	67	63	60	67	63	60	59	59	59	59	59	59	59	59	59																			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P205279

CATALOG NUMBER: LSR6B15D010BZ EC6B10208027 6LBNLI1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	211.1	18.9
10°-20°	379.0	34.0
20°-30°	306.4	27.5
30°-40°	176.5	15.8
40°-50°	37.3	3.3
50°-60°	3.2	0.3
60°-70°	1.6	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	896.6	80.4
0°-40°	1073.1	96.2
0°-60°	1113.6	99.8
0°-90°	1115.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1115.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2540	
5°	2366	211
15°	1377	379
25°	661	306
35°	280	177
45°	40	37
55°	3	3
65°	2	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P205279

CATALOG NUMBER: LSR6B15D010BZ EC6B10208027 6LBNLI1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2539.6
2.5°	2509.1
5°	2365.9
7.5°	2160.0
10°	1907.5
12.5°	1648.6
15°	1376.8
17.5°	1114.6
20°	923.2
22.5°	776.8
25°	661.0
27.5°	562.9
30°	474.5
32.5°	376.4
35°	279.9
37.5°	194.6
40°	127.1
42.5°	77.2
45°	40.2
47.5°	16.1
50°	4.8
52.5°	4.8
55°	3.2
57.5°	3.2
60°	1.6
62.5°	1.6
65°	1.6
67.5°	1.6
70°	1.6
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)